


Nutsetters



EAN:	4013288016584	Size:	65x14x14 mm
Part number:	05060280001	Weight:	33 g
Article number:	869/4	Country of origin:	CZ
		Customs tariff number:	82042000

- Nutsetter for hexagon head screws
- Non-magnetic design
- Metric
- 1/4" hexagon drive

Non-magnetic design. 1/4" hexagon, suitable for holders as per DIN ISO 1173-F 6.3.

Web link

https://products.wera.de/en/bits_holders_adaptors_and_sets_the_range_of_bits_nutsetters_869_4.html

Wera - 869/4
05060280001 - 4013288016584

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

869/4 Nutsetters, 9 x 65 mm

Nutsetters



Non-magnetic design



Non-magnetic nutsetters that do not attract metal filings.

Web link





https://products.wera.de/en/bits HOLDERS_adaptors_and_sets_the_range_of_bits_nutsetters_869_4.html

Wera - 869/4

05060280001 - 4013288016584

Nutsetters

Further versions in this product family:

	 mm	 inch	 mm	 mm
05060400001	5.5	-	50.0	11.0
05060272001	5.5	-	65.0	9.0
05060401001	6.0	-	50.0	11.0
05060274001	6.0	-	65.0	11.0
05060402001	7.0	-	50.0	11.0
05060276001	7.0	-	65.0	11.0
05060403001	8.0	-	50.0	12.5
05060278001	8.0	-	65.0	12.5
05060404001	9.0	-	50.0	14.0
05060280001	9.0	-	65.0	14.0
05060405001	10.0	-	50.0	14.0
05060282001	10.0	-	65.0	14.0
05060406001	11.0	-	50.0	16.0
05060281001	11.0	-	65.0	16.0
05060407001	12.0	-	50.0	18.0
05060283001	12.0	-	65.0	18.0
05060408001	13.0	-	50.0	18.0
05060284001	13.0	-	65.0	19.0
05060409001	-	1/4"	50.0	11.0
05060286001	-	1/4"	65.0	11.0
05060410001	-	5/16"	50.0	12.5
05060290001	-	5/16"	65.0	12.5
05060411001	-	3/8"	50.0	14.0
05060288001	-	3/8"	65.0	14.0
05060412001	-	7/16"	50.0	16.0

Web link

https://products.wera.de/en/bits HOLDERS_adaptors_and_sets_the_range_of_bits_nutsetters_869_4.html

Wera - 869/4

05060280001 - 4013288016584

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de