


## 840/4 Z bits, 9/64" x 89 mm

### Bits for Hexagon Socket Screws



|                        |                  |                               |           |
|------------------------|------------------|-------------------------------|-----------|
| <b>EAN:</b>            | 4013288155511    | <b>Size:</b>                  | 89x7x6 mm |
| <b>Part number:</b>    | 05059664001      | <b>Weight:</b>                | 25 g      |
| <b>Article number:</b> | 840/4 Z Hex-Plus | <b>Country of origin:</b>     | CZ        |
|                        |                  | <b>Customs tariff number:</b> | 82079030  |

- For socket head screws
- Hex-Plus allows socket head screws to live longer
- Tough for hard materials
- 1/4" hexagon drive (Wera connecting series 4)

Tough Wera bits for hexagonal socket screws, for universal use. Hex-Plus offers larger contact surfaces in the screw head. The notch effect is reduced to a minimum and the destruction of the screw is nearly eliminated. 1/4" hexagonal, suitable for holders as per DIN ISO 1173-F 6.3.

#### Web link

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_and\\_sets\\_the\\_range\\_of\\_bits\\_bits\\_for\\_hexagon\\_socket\\_screws\\_840\\_4\\_z\\_hex-plus.html](https://products.wera.de/en/bits_holders_adaptors_and_sets_the_range_of_bits_bits_for_hexagon_socket_screws_840_4_z_hex-plus.html)

Wera - 840/4 Z Hex-Plus  
05059664001 - 4013288155511

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## Hex-Plus

## Tough-absorbing bits








Hexagon socket screws are a problem, because the contact surfaces that transfer the force of the tool to the screw are very narrow. The consequence: the head of the screw can be damaged, usually rounding out the recess. Hex-Plus tools have larger contact surfaces to prevent this, driving from the flats of the recess, rather than the corners. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

## Further versions in this product family:

|                           |  |  |  |  |  |
|---------------------------|---|---|---|---|---|
|                           | mm  | inch  | mm  | inch  | mm  |
| 05160885001               | 0.9   | -   | 50  | 2"  | 2.6   |
| 05059602001               | 1.5   | -   | 50  | 2"  | 2.0   |
| 05059603001               | 2.0   | -   | 50  | 2"  | 4.0   |
| 05059628001               | 2.0   | -   | 89  | 3 1/2"  | 4.0   |
| 05059604001               | 2.5   | -   | 50  | 2"  | 4.0   |
| 05059629001               | 2.5   | -   | 89  | 3 1/2"  | 4.0   |
| 05059605001               | 3.0   | -   | 50  | 2"  | 4.0   |
| 05059630001               | 3.0   | -   | 89  | 3 1/2"  | 4.0   |
| 05380033001               | 3.0   | -   | 152   | 6"  | 4.0   |
| 05059610001               | 4.0   | -   | 50  | 2"  | 5.0   |
| 05059631001               | 4.0   | -   | 89  | 3 1/2"  | 5.0   |
| 05059634001               | 4.0   | -   | 152   | 6"  | 5.0   |
| 05059615001               | 5.0   | -   | 50  | 2"  | 6.0   |
| 05059632001               | 5.0   | -   | 89  | 3 1/2"  | 6.0   |
| 05059635001               | 5.0   | -   | 152   | 6"  | 6.0   |
| 05059620001 <sup>1)</sup> | 6.0   | -   | 50  | 2"  | 5.0   |

## Web link

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_and\\_sets\\_the\\_range\\_of\\_bits\\_bits\\_for\\_hexagon\\_socket\\_screws\\_840\\_4\\_z\\_hex-plus.html](https://products.wera.de/en/bits_holders_adaptors_and_sets_the_range_of_bits_bits_for_hexagon_socket_screws_840_4_z_hex-plus.html)

Wera - 840/4 Z Hex-Plus  
 05059664001 - 4013288155511

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: [info@wera.de](mailto:info@wera.de)

## Bits for Hexagon Socket Screws

|                           |          |              |           |               |            |
|---------------------------|----------|--------------|-----------|---------------|------------|
| 05059633001 <sup>1)</sup> | 6.0      | -            | 89        | 3 1/2"        | -          |
| 05059636001 <sup>1)</sup> | 6.0      | -            | 152       | 6"            | -          |
| 05059625001 <sup>1)</sup> | 8.0      | -            | 50        | 2"            | -          |
| 05059637001 <sup>1)</sup> | 8.0      | -            | 89        | 3 1/2"        | -          |
| 05350430001               | -        | 0.05"        | 50        | 2"            | 2.5        |
| 05135090001               | -        | 1/16"        | 50        | 2"            | 2.5        |
| 05135091001               | -        | 5/64"        | 50        | 2"            | 3.0        |
| 05059660001               | -        | 5/64"        | 89        | 3 1/2"        | 3.0        |
| 05135092001               | -        | 3/32"        | 50        | 2"            | 3.0        |
| 05059661001               | -        | 3/32"        | 89        | 3 1/2"        | 3.5        |
| 05135093001               | -        | 7/64"        | 50        | 2"            | 3.5        |
| 05059662001               | -        | 7/64"        | 89        | 3 1/2"        | 4.0        |
| 05135094001               | -        | 1/8"         | 50        | 2"            | 4.0        |
| 05059663001               | -        | 1/8"         | 89        | 3 1/2"        | 4.0        |
| 05380045001               | -        | 1/8"         | 152       | 6"            | 4.0        |
| 05135095001               | -        | 9/64"        | 50        | 2"            | 4.5        |
| <b>05059664001</b>        | <b>-</b> | <b>9/64"</b> | <b>89</b> | <b>3 1/2"</b> | <b>4.5</b> |
| 05380046001               | -        | 9/64"        | 152       | 6"            | 4.5        |
| 05135096001               | -        | 5/32"        | 50        | 2"            | 5.0        |
| 05059665001               | -        | 5/32"        | 89        | 3 1/2"        | 5.0        |
| 05380047001               | -        | 5/32"        | 152       | 6"            | 5.0        |
| 05135097001               | -        | 3/16"        | 50        | 2"            | 6.0        |
| 05059666001               | -        | 3/16"        | 89        | 3 1/2"        | 6.0        |
| 05380048001               | -        | 3/16"        | 152       | 6"            | 6.0        |
| 05135098001               | -        | 7/32"        | 50        | 2"            | -          |
| 05059667001               | -        | 7/32"        | 89        | 3 1/2"        | -          |
| 05380049001               | -        | 7/32"        | 152       | 6"            | -          |
| 05135099001               | -        | 1/4"         | 50        | 2"            | -          |
| 05059668001               | -        | 1/4"         | 89        | 3 1/2"        | -          |
| 05380050001               | -        | 1/4"         | 152       | 6"            | -          |
| 05346288001               | -        | 5/16"        | 50        | 2"            | -          |

1) Hexagonal blade

## Web link

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_and\\_sets\\_the\\_range\\_of\\_bits\\_bits\\_for\\_hexagon\\_socket\\_screws\\_840\\_4\\_z\\_hex-plus.html](https://products.wera.de/en/bits_holders_adaptors_and_sets_the_range_of_bits_bits_for_hexagon_socket_screws_840_4_z_hex-plus.html)

Wera - 840/4 Z Hex-Plus  
05059664001 - 4013288155511

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de