Kraftform Kompakt 60, 62


















Part number: 05071117001 Weight: 510 g Article number: KK 60 Stainless Imperial Country of origin: CZ

> **Customs tariff** 82079030

number:



- Vacuum ice-hardening provides the required hardness and strength
- Handle/Interchangeable blade system for rapid exchange of the blade
- Rapidaptor technology for rapid bit change
- Storage and transport in a robust belt pouch

Pouch with bits in a length of 89 mm. Includes Kraftform holder 3816 R with Rapidaptor guick-release chuck and multi-component Kraftform handle for low-fatigue working. Stainless design to prevent the formation of extraneous rust.











Kraftform Kompakt 60, 62




Screw stainless steel together with stainless steel!



Solution to the rust problem: screwdriving stainless steel together with stainless steel! Wera stainless steel tools are manufactured out of stainless steel so unsightly rust can be avoided.

Vacuum ice-hardened



The stainless steel tools from Wera are vacuum ice-hardened and have the hardness and strength needed for screw connections. There are no limitations to the industrial applications they are suitable for.

Handle/interchangeable blade system



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

Chuck-all



The Rapidaptor quick-release chucks hold ¼" DIN ISO 1173-C 6,3 and E 6,3 as well as Wera series 1 and 4 bits.

Rapid-in and self-lock



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

Rapid-out




Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

Prevents hand injuries



The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

Storage and transport



The tools can be stored and carried in a robust belt pouch, keeping them always to hand.

Kraftform Kompakt 60, stainless, Imperial, 17 pieces

Kraftform Kompakt 60, 62



Set contents:

3816 R Bitholding screwdriver with Rapidaptor quick-release chuck, stainless, 1/4" x 119 mm

(a) 05051465001 1x 1/4" x 119 mm



3851/4 Bits, stainless, PH 1 x 89 mm

•	05071081001	1x	PH 1 x 89 mm
	05071082001	1x	PH 2 x 89 mm
	050710830011)	1x	PH 3 x 89 mm
	Hexagonal blade		

3867/4 TORX® BO bits with bore hole, stainless, TX 10 x 89 mm

⊙	05071089001	1x	TX 10 x 89 mm
Inv K	05071090001	1x	TX 15 x 89 mm
	05071091001	1x	TX 20 x 89 mm
	05071092001	1x	TX 25 x 89 mm
	05071094001	1x	TX 30 x 89 mm

3800/4 Bits, stainless, 1 x 5.5 x 89 mm

	05071080001	1x	1 x 5.5 x 89 mm
Tree			

3840/4 Bits, stainless, 3/32" x 89 mm

0	05071105001	1x	3/32" x 89 mm
(m)	05071106001	1x	1/8" x 89 mm
	05071107001	1x	5/32" x 89 mm
	05071108001	1x	3/16" x 89 mm

3868/4 Square-Plus bits, stainless, # 1 x 89 mm

0	05071097001	1x	# 1 x 89 mm
- Inches	05071098001	1x	# 2 x 89 mm
	05071099001	1x	# 3 x 89 mm

Web link

 $https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_60_62_kk_60_stainless_imperial.html$