

Series 7400 ESD Krafftform adjustable torque screwdrivers (0.1-3.0 Nm) with Rapidaptor quick-release chuck, 7432 ESD x 0.90-1.50 Nm  
Series 7400 ESD Krafftform Torque Screwdrivers



<b>EAN:</b>	4013288179173	<b>Size:</b>	155x37x37 mm
<b>Part number:</b>	05074784001	<b>Weight:</b>	122 g
<b>Article number:</b>	7400 ESD	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000

- Adjustable Krafftform ESD torque screwdriver with Rapidaptor quick-release chuck
- ESD-safe tool thanks to surface resistance of  $\leq 10^9$  Ohm
- Multi-component Krafftform handle for fast and low-fatigue working
- Hexagonal anti-roll feature against rolling away
- Rapidaptor quick-release chuck for bits with 1/4" hex head drive

Wera torque screwdriver. Dependable protection against electrostatic energy and associated damage. Variable torque setting option with highest precision. Simple adjustment of the required torque value without any special tools. Easy-to-read scale value. Rapidaptor quick-release technology for rapid bit change. Unlimited torque to loosen seized screws. Multi-component Krafftform handle with hard and soft zones for high working speeds, whilst being easy on the hand. Suitable for bits with 1/4" hexagon head drive as per DIN ISO 1173-C 6.3 and E 6.3 (ISO 1173).



**Web link**

[https://products.wera.de/en/torque\\_tools\\_series\\_7400\\_esd\\_krafftform\\_torque\\_screwdrivers\\_7400\\_esd.html](https://products.wera.de/en/torque_tools_series_7400_esd_krafftform_torque_screwdrivers_7400_esd.html)

Wera - 7400 ESD  
05074784001 - 4013288179173

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

Series 7400 ESD Krafftform adjustable torque screwdrivers (0.1-3.0 Nm) with Rapidaptor quick-release chuck, 7432 ESD x 0.90-1.50 Nm  
Series 7400 ESD Krafftform Torque Screwdrivers



Adjustable Torque Screwdrivers

Wera ESD Tools

Simple setting

Easy-to-read



Wera's adjustable torque screwdrivers allow variable torque settings with maximum precision and ensure that the user gets the very best results in the familiar Wera design with superior ergonomics.

The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

Simple setting of the required torque by hand.


Easy-to-read scale value.

Attachable magnifying glass

Measurement accuracy

Unlimited torque

Versatile



Articles 7430, 7431 and 7432 all come with a magnifying glass. This can be easily attached on to the scale, dramatically improving visibility.

Measurement accuracy is  $\pm 6\%$  (article 1430:  $\pm 10\%$ ) in accordance with the standard DIN EN ISO 6789. Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.

Unlimited torque for loosening seized screws.

Rapidaptor technology makes the tool adaptable since bits and sockets can be exchanged rapidly.

Web link

[https://products.wera.de/en/torque\\_tools\\_series\\_7400\\_esd\\_krafftform\\_torque\\_screwdrivers\\_7400\\_esd.html](https://products.wera.de/en/torque_tools_series_7400_esd_krafftform_torque_screwdrivers_7400_esd.html)







Wera - 7400 ESD  
05074784001 - 4013288179173

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

Series 7400 ESD Kraftform adjustable torque screwdrivers (0.1-3.0 Nm) with  
 Rapidaptor quick-release chuck, 7432 ESD x 0.90-1.50 Nm  
 Series 7400 ESD Kraftform Torque Screwdrivers



Further versions in this product family:

	art. no.	 inch	 Nm	 Nm	 mm	 mm	 inch	
	05074780001 <sup>1)</sup>	7430 ESD	1/4"	0.10-0.34	0.015	89	142	5 7/16"
	05074782001 <sup>1)</sup>	7431 ESD	1/4"	0.30-1.00	0.05	89	142	5 7/16"
	<b>05074784001<sup>1)</sup></b>	<b>7432 ESD</b>	<b>1/4"</b>	<b>0.90-1.50</b>	<b>0.05</b>	<b>89</b>	<b>142</b>	<b>5 7/16"</b>
	05074730001	7440 ESD	1/4"	0.3-1.2	0.05	105	155	6"
	05074731001	7441 ESD	1/4"	1.2-3.0	0.10	105	155	6"

1) With attachable magnifying glass, dramatically improving visibility.

Web link

[https://products.wera.de/en/torque\\_tools\\_series\\_7400\\_esd\\_kraftform\\_torque\\_screwdrivers\\_7400\\_esd.html](https://products.wera.de/en/torque_tools_series_7400_esd_kraftform_torque_screwdrivers_7400_esd.html)

Wera - 7400 ESD  
 05074784001 - 4013288179173

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: info@wera.de