

Series 7400 ESD Krafftform torque screwdrivers with a customised factory pre-set measurement value, handle size 105 mm, 7460 ESD x 0.3-1.2 Nm  
7400 ESD series Krafftform Torque screwdrivers, with factory pre-set value of your choice



<b>EAN:</b>	4013288188236	<b>Size:</b>	155x37x37 mm
<b>Part number:</b>	05074840010	<b>Weight:</b>	126 g
<b>Article number:</b>	7400 ESD customized pre-set, 105 mm	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000

- Customized pre-set torque screwdriver with Rapidaptor quick-release chuck
- ESD-safe tool thanks to surface resistance of  $\leq 10^9$  Ohm
- Suitable for bits with 1/4" hex head drive
- Rapidaptor quick-release chuck for bits with 1/4" hex head drive
- Rapidaptor technology for rapid bit change
- Krafftform handle for fast and ergonomic screwdriving

Wera torque screwdriver. Safe protection against electrostatic charge and associated damage. With a customised factory pre-set torque value. For all applications, where the same constant torque and repeat accuracy are required. The torque can be changed with an extra tool within the measuring range (re-calibration kit can be ordered with the code number 05137001001). Afterwards you can check the set value using an off-the-shelf torque tester. Rapidaptor quick-release technology for rapid bit changes. Unlimited loosening torque for slackening stuck screws. Multi-component Krafftform handle with hard and soft zones for high working speeds, whilst being easy on the hand. Suitable for bits with a 1/4" external hexagon drive as per DIN ISO 1173-C 6.3 and E 6.3 (ISO 1173).  
Please note: 1 Ncm = 0.01 Nm.



**Web link**

[https://products.wera.de/en/torque\\_tools\\_7400\\_esd\\_series\\_krafftform\\_torque\\_screwdrivers\\_with\\_factory\\_pre-set\\_value\\_of\\_your\\_choice\\_7400\\_esd\\_customized\\_pre-set\\_105\\_m](https://products.wera.de/en/torque_tools_7400_esd_series_krafftform_torque_screwdrivers_with_factory_pre-set_value_of_your_choice_7400_esd_customized_pre-set_105_m)


Wera - 7400 ESD customized pre-set, 105 mm  
05074840010 - 4013288188236

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

Series 7400 ESD Krafftform torque screwdrivers with a customised factory pre-set measurement value, handle size 105 mm, 7460 ESD x 0.3-1.2 Nm  
7400 ESD series Krafftform Torque screwdrivers, with factory pre-set value of your choice



Customised pre-setting



Wera torque screwdriver. With a customised factory pre-set torque value. For all applications, where the same constant torque and repeat accuracy are required.

Wera ESD Tools



The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

High protection



The electric surface resistance of the Wera ESD material is  $\leq 10^9$  ohm. This securely protects components against electrostatic energy and associated damage.

Versatile



Rapidaptor technology makes the tool adaptable since bits and sockets can be exchanged rapidly.

Chuck-all



The Rapidaptor quick-release chucks hold 1/4" DIN ISO 1173-C 6,3 and E 6,3 as well as Wera series 1 and 4 bits.

Rapid-in and self-lock



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

Rapid-out



Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

Prevents hand injuries



The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

Web link

[https://products.wera.de/en/torque\\_tools\\_7400\\_esd\\_series\\_krafftform\\_torque\\_screwdrivers\\_with\\_factory\\_pre-set\\_value\\_of\\_your\\_choice\\_7400\\_esd\\_customized\\_pre-set\\_105\\_m](https://products.wera.de/en/torque_tools_7400_esd_series_krafftform_torque_screwdrivers_with_factory_pre-set_value_of_your_choice_7400_esd_customized_pre-set_105_m)


Wera - 7400 ESD customized pre-set, 105 mm  
05074840010 - 4013288188236

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

Series 7400 ESD Kraftform torque screwdrivers with a customised factory pre-set measurement value, handle size 105 mm, 7460 ESD x 0.3-1.2 Nm  
7400 ESD series Kraftform Torque screwdrivers, with factory pre-set value of your choice



Further versions in this product family:

						
art. no.		inch	Nm	mm	mm	inch
05074840010 <sup>1)</sup>	7460 ESD	1/4"	0.3-1.2	105	133	5 15/64"
05074842010 <sup>1)</sup>	7461 ESD	1/4"	1.2-3.0	105	155	6 7/64"

1) The desired settings can be made in the following units: Nm, kgf. m, lbf. ft., ozf. in., dN. m, kgf. cm, lbf. in, in. oz, cN. m, gf. m, ft. lb, gf. cm, in. lb.

**Web link**

[https://products.wera.de/en/torque\\_tools\\_7400\\_esd\\_series\\_kraftform\\_torque\\_screwdrivers\\_with\\_factory\\_pre-set\\_value\\_of\\_your\\_choice\\_7400\\_esd\\_customized\\_pre-set\\_\\_105\\_m](https://products.wera.de/en/torque_tools_7400_esd_series_kraftform_torque_screwdrivers_with_factory_pre-set_value_of_your_choice_7400_esd_customized_pre-set__105_m)

Wera - 7400 ESD customized pre-set, 105 mm  
05074840010 - 4013288188236

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de