


7775 Open ring spanner insert, 9x12 mm, 9x12 x 19 x 49 mm

Insert tools ring spanners



EAN:	4013288196422	Size:	122x83x16 mm
Part number:	05078657001	Weight:	82 g
Article number:	7775	Country of origin:	TW
		Customs tariff number:	82079099

- Square insert tool 9x12 mm
- For torque wrenches of the Click-Torque X series with 9x12 mm holder
- Application: Hexagon screw heads or nuts
- With safety pin
- The chrome-vanadium steel version makes the plug-in tools suitable for heavy loads

Open ring spanner insert, for hexagon screw heads or nuts; for torque wrenches of the Click-Torque X series with 9x12 mm holder.

Web link

https://products.wera.de/en/torque_tools_series_click-torque_wrenches_series_insert_tools_insert_tools_ring_spanners_7775.html

Wera - 7775
05078657001 - 4013288196422

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Insert tools ring spanners

Drive 9x12 mm

With safety pin

Chrome vanadium steel



For torque wrenches of the Click-Torque X series with 9x12 mm holder.



The safety pin of the insert tools enables safe working and fast tool change.



The chrome-vanadium steel version makes the plug-in tools suitable for heavy loads.

Further versions in this product family:



mm



mm



mm



mm



mm



mm



mm

05078650001	9x12	10	17.5	44.0	27.0	22.0	11.0
05078651001	9x12	11	17.5	44.0	27.0	22.0	11.0
05078652001	9x12	12	17.5	44.0	27.0	22.0	11.0
05078653001	9x12	13	17.5	44.0	27.0	22.0	11.0
05078654001	9x12	14	17.5	44.0	27.0	22.0	11.0
05078655001	9x12	17	17.5	44.0	27.0	22.0	11.0
05078656001	9x12	18	17.5	49.0	32.0	33	15.0
05078657001	9x12	19	17.5	49.0	32.0	33	15.0
05078658001	9x12	22	17.5	49.0	32.0	33	15.0

Web link

https://products.wera.de/en/torque_tools_series_click-torque_wrenches_series_insert_tools_insert_tools_ring_spanners_7775.html

Wera - 7775

05078657001 - 4013288196422

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de