Series Kraftform Micro





EAN:	4013288031945
Part number:	05118150001
Article number:	2035/6 A

Size:	250x205x50 mm	
Weight:	398 g	
Country of origin:	CZ	
Customs tariff number:	82054000	

- Kraftform Micro screwdriver for slotted and cross-recess screws, Phillips
- Multi-component Kraftform Micro handle for fast and ergonomic screwdriving
- · Anti-roll feature and swivel cap for rapid twisting
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Take it easy tool finder: colour coding according to profile and size
- E.g. for electricians, opticians, precision mechanics, jewellers or IT hardware fitters

High quality Wera Micro screwdriver set for precision mechanical work. Rapid twisting is possible by fixing the hand on the twist cap and using the fast-turning zone just below it. This makes time-consuming grip adjustments unnecessary. Power zone with integrated soft zones ensure the transfer of higher tightening and loosening torque. Precision zone for the right angle for adjustment work. The Wera Black Point tip offers high corrosion protection and an exact fit. Includes practical rack for tidy storage of the screwdrivers.

















Series Kraftform Micro



The precision zone



Screwdriving jobs in electrical and precision engineering applications are often tedious and timeconsuming. We learned from users what is important for them: working speeds, torque, precision - and we then focused particularly on these issues.

Kraftform Micro handle



Multi-component screwdriver handle for ergonomic working.


The refined screwdriver for electronics technicians




The Kraftform Micro, with its three zones and their specific arrangement, satisfies these requirements perfectly. The freeturning cap that provides support for the hand works with these advantages, enabling quick and easy precision work.

The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

The power zone




The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.





The fast-turning zone just below the rotating cap allows rapid twisting.

Wera Black Point tip



The Wera Black Point tip and a refined hardening process ensure long service life of the tip, improved corrosion protection and an exact fit.

Applications



Indispensable for many users, including electronics technicians, opticians, precision engineers, jewellers, EDP hardware fitters and model-makers

Series Kraftform Micro

Set contents:

2050 PH Screwdriver for Phillips screws for electronic applications, PH 00 x 60 mm

0

051180200011)	1x	PH 00 x 60 mm
0511802200120	1x	PH 0 x 60 mm
1) Optimised for Asian PH screws		

1) Optimised for Asian PH screws 2) Size 0 modified according to JCIS 0 (Japanese Camera Industrial Standard)

2035 Screwdriver for slotted screws for electronic applications, 0.30 x 1.8 x 60 mm



05118004001 1x 0.30 x 1.8 x 60 mm 05118006001 05118008001 05118010001

1x 0.40 x 2 x 60 mm 1x 0.40 x 2.5 x 80 mm 1x 0.50 x 3 x 80 mm

