

840/4 Z bits, 1/16" x 50 mm

Bits for Hexagon Socket Screws



EAN:	4013288107053	Size:	50x7x6 mm
Part number:	05135090001	Weight:	6 g
Article number:	840/4 Z Hex-Plus	Country of origin:	CZ
		Customs tariff number:	82079030

- For socket head screws
- Ductile and tough for hard materials
- Hex-Plus allows socket head screws to live longer
- 1/4" hexagon drive (Wera connecting series 4)
- Suitable for AEG, ARO, Atlas-Copco, Biax, Black & Decker, Bosch, Buckeye Tools etc.

Tough viscous Wera bits for hexagon socket screws for universal use. The Hex-Plus profile offers a greater contact surface in the head of the screw. The notching effect is therefore reduced to a minimum and damage to the screw head more or less eliminated. 1/4" hexagon, suitable for holders as per DIN ISO 1173-F 6.3.

Web link

https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_hexagon_socket_screws_840_4_z_hex-plus.html

Wera - 840/4 Z Hex-Plus
05135090001 - 4013288107053

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Hex-Plus

Tough-absorbing bits








Hexagon socket screws are a problem, because the contact surfaces that transfer the force of the tool to the screw are very narrow. The consequence: the head of the screw can be damaged, usually rounding out the recess. Hex-Plus tools have larger contact surfaces to prevent this, driving from the flats of the recess, rather than the corners. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

Further versions in this product family:

	 mm	 inch	 mm	 inch	 mm
05160885001	0.9		50	2	2.6
05059602001	1.5		50	2	2.0
05059603001	2.0		50	2	4.0
05059628001	2.0		89	3 1/2	4.0
05059604001	2.5		50	2	4.0
05059629001	2.5		89	3 1/2	4.0
05059605001	3.0		50	2	4.0
05059630001	3.0		89	3 1/2	4.0
05380033001	3.0		152	6	4.0
05059610001	4.0		50	2	5.0
05059631001	4.0		89	3 1/2	5.0
05059634001	4.0		152	6	5.0
05059615001	5.0		50	2	6.0
05059632001	5.0		89	3 1/2	6.0
05059635001	5.0		152	6	6.0
05059620001	6.0		50	2	5.0

Web link

https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_hexagon_socket_screws_840_4_z_hex-plus.html

Wera - 840/4 Z Hex-Plus
 05135090001 - 4013288107053

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Bits for Hexagon Socket Screws

05059633001	6.0		89	3 1/2	-
05059636001	6.0		152	6	-
05059625001	8.0		50	2	-
05059637001	8.0		89	3 1/2	-
05350430001		0.05	50	2	2.5
05135090001		1/16"	50	2	2.5
05135091001		5/64"	50	2	3.0
05059660001		5/64"	89	3 1/2	3.0
05135092001		3/32"	50	2	3.0
05059661001		3/32"	89	3 1/2	3.5
05135093001		7/64"	50	2	3.5
05059662001		7/64"	89	3 1/2	4.0
05135094001		1/8"	50	2	4.0
05059663001		1/8"	89	3 1/2	4.0
05380045001		1/8"	152	6	4.0
05135095001		9/64"	50	2	4.5
05059664001		9/64"	89	3 1/2	4.5
05380046001		9/64"	152	6	4.5
05135096001		5/32"	50	2	5.0
05059665001		5/32"	89	3 1/2	5.0
05380047001		5/32"	152	6	5.0
05135097001		3/16"	50	2	6.0
05059666001		3/16"	89	3 1/2	6.0
05380048001		3/16"	152	6	6.0
05135098001		7/32"	50	2	-
05059667001		7/32"	89	3 1/2	-
05380049001		7/32"	152	6	-
05135099001		1/4"	50	2	-
05059668001		1/4"	89	3 1/2	-
05380050001		1/4"	152	6	-
05346288001		5/16	50	2	-

Web link

https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_hexagon_socket_screws_840_4_z_hex-plus.html

Wera - 840/4 Z Hex-Plus
05135090001 - 4013288107053

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de