

2054 Screwdriver for hexagon socket screws for electronic applications, 1/16" x 60 mm
Series Kraftform Micro



EAN:	4013288032157	Size:	157x13x13 mm
Part number:	05118076001	Weight:	14 g
Article number:	2054 Micro	Country of origin:	CZ
		Customs tariff number:	82054000

- Kraftform Micro screwdriver for hexagon socket screws
- Multi-component Kraftform Micro handle for fast and ergonomic screwdriving
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Hex-Plus allows socket head screws to live longer
- Take it easy tool finder: colour coding according to profile and size
- E.g. for electricians, opticians, precision mechanics, jewellers or IT hardware fitters

Premium Wera Micro screwdriver for precision mechanical couplings. By supporting the hand on the rotating cap, and due to the fast rotating zone below the rotating cap, lightning fast turning is possible. Time-consuming hand switching is eliminated. The power zone with integrated soft zones ensures the transmission of high tightening and loosening moments. Precision zone for correct rotation angles whilst adjusting. The Wera Black Point tip offers fitting accuracy and optimised corrosion protection. "Take it easy" tool finder with size stamping and colour coding by profile for quick and easy identification of the required tool.



Web link

https://products.wera.de/en/screwdrivers_series_kraftform_micro_2054_micro.html

Wera - 2054 Micro
05118076001 - 4013288032157

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Hex-Plus



Screwdriving jobs in electrical and precision engineering applications are often tedious and time-consuming. We learned from users what is important for them: working speeds, torque, precision - and we then focused particularly on these issues.




Hexagon screws can endure a problem because the contact surfaces delivering the power from the conventional tool, is transferred to the screw via very small surface areas. The consequence: the screw can become damaged (rounding out). Hex-Plus tools have a greater contact surface that prevents this from happening! At the same time, as much as 20 % more torque can be applied. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!

Kraftform Micro handle




Multi-component screwdriver handle for ergonomic working.

The refined screwdriver for electronics technicians




The Kraftform Micro, with its three zones and their specific arrangement, satisfies these requirements perfectly. The free-turning cap that provides support for the hand works with these advantages, enabling quick and easy precision work.

The precision zone




The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

The power zone




The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

The fast-turning zone



The fast-turning zone just below the rotating cap allows rapid twisting.

"Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Web link

https://products.wera.de/en/screwdrivers_series_kraftform_micro_2054_micro.html

Wera - 2054 Micro
05118076001 - 4013288032157

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de







2054 Screwdriver for hexagon socket screws for electronic applications, 1/16" x 60

mm

Series Kraftform Micro



Further versions in this product family:

						
	mm	inch	mm	mm	mm	inch
05118060001	0.7	-	40	97	3.0	1 9/16"
05118062001	0.9	-	40	97	3.0	1 9/16"
05118064001	1.3	-	40	97	3.0	1 9/16"
05118066001	1.5	-	60	97	3.0	2 3/8"
05118068001	2	-	60	97	3.0	2 3/8"
05118070001	2.5	-	60	97	4.0	2 3/8"
05118072001	3.0	-	60	97	4.0	2 3/8"
05345284001	-	0,028"	40	97	3.0	1 9/16"
05345285001	-	0,035"	40	97	3.0	1 9/16"
05118074001	-	0.05"	40	97	3.0	1 9/16"
05118076001	-	1/16"	60	97	3.0	2 3/8"
05118078001	-	5/64"	60	97	3.0	2 3/8"
05118080001	-	3/32"	60	97	4.0	2 3/8"
05118082001	-	7/64"	60	97	4.0	2 3/8"
05118075001	-	1/8"	60	97	4.0	2 3/8"

Web link

https://products.wera.de/en/screwdrivers_series_kraftform_micro_2054_micro.html

Wera - 2054 Micro

05118076001 - 4013288032157

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de