

Kraftform Kompakt SH 1 PlumbKit, 25 pieces

Kraftform Kompakt user-specific sets



EAN: 4013288170132
Part number: 05135927001
Article number: Kraftform Kompakt SH 1

Size: 300x220x65 mm
Weight: 1694 g
Country of origin: CZ
Customs tariff number: 82054000

- JOKER combination ratcheting wrench with special holding plate against slipping/loss of the screw
- Zyklop Speed ratchet for fast and powerful working
- Insulated Kraftform VDE slotted screwdriver for safe work at 1,000 volts
- Kraftform Chiseldriver with hex blade extending through handle and integrated impact cap
- Hollow shaft nutspinner for nuts on protruding threaded rods
- Also suitable for Würth ASSY screws as well as Altenloh SPAX T-STAR plus screws

Compact tool set with the 25 most important screwdriving tools for plumbing and heating applications. Includes 2 JOKER open-end wrenches, the 1/4" Zyklop ratchet and accessories, 6 x 89 mm bits, 5 multi-component Kraftform Plus screwdrivers and single-pole phase tester. Two JOKER combination ratcheting wrenches with special holding plate against slipping/loss of the screw and more torque transfer; 1 Zyklop ratchet 8000 A (1/4") for fast, powerful working; 3 Zyklop sockets 8790 HMA for manual and power tools usage; 1 Zyklop adaptor 8784 A1 for bits; 6 TORX® HF bits 867/4 with holding function for TORX® screws for secure carry without any loss of the screws; the Wera 867/4 TX HF bits are also suitable for Würth ASSY screws as well as Altenloh SPAX T-STAR plus screws; 1 single-pole phase tester 247; 2 Kraftform series 100 slotted screwdrivers 160 i and 160 is for safe work up to 1,000 volts (160 is with reduced shaft diameter and integrated insulation protection for reaching and actuating low-lying screws and spring elements); 1 Kraftform Chiseldriver 932 A (slotted) with hex blade extending right through the handle and integrated impact cap for screwdriving and simpler chiselling work; 2 nutsetters 395 HO with hollow shaft for the tightening or loosening of screws on long bolts as well as seized screws. Take it easy tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool.



Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_user-specific_sets_kraftform_kompakt_sh_1.html

Wera - Kraftform Kompakt SH 1
 05135927001 - 4013288170132

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Kraftform Kompakt user-specific sets

Special sets



Kraftform Kompakt user ranges - the new special sets - compact yet very versatile. Suitable for all sanitary, wood, metal or electrical applications.

Kraftform Kompakt SH 1 PlumbKit



Compact tool set with the 25 most important screwdriving tools for plumbing and heating applications.

Joker open-ended wrench



When we began to think about open-ended wrenches, we asked ourselves: why does the wrench always have to be flipped over; why does it have an offset design; why does it slip off injuring fingers? The new design of the open end resulted in a real "Joker" that works even when all other trumps have been played.

Zyklop "6 in 1"



1. Fine-tooth ratchet 2. Flex-head ratchet 3. Angle ratchet 4. Quick-release ratchet 5. Power ratchet 6. Screwdriver

Fast movers




The Zyklop Speed ratchets are really fast movers. The gyrating mass design means that screwdriving is accelerated. The rotation-symmetric structure of the Kraftform handle and the free-turning sleeve reinforce this rapid twisting process, particularly when the ratchet does not engage due to too little resistance in the thread.

Hollow shaft nutsetter




A screwdriver with a hollow shaft is needed whenever there are screwdriving jobs involving threaded rods i.e. the threaded rod can slip into the hollow shaft of the nutsetter.

VDE-insulated screwdriver with reduced blade diameter



Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

Kraftform Kompakt



Why is the right tool so often not at hand? The reason: too many tools and overly-heavy tool bags can make it bothersome to carry them onsite. So for us it was a clear challenge: to design a tool that is suitable for a whole host of applications and can be easily taken along to jobs at other sites. Our solution: Kraftform Kompakt tools. A handle into which blades with a range of different profiles can be inserted. Compactly and protectively housed in a light and robust textile pouch or plastic box.

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_user-specific_sets_kraftform_kompakt_sh_1.html

Wera - Kraftform Kompakt SH 1
05135927001 - 4013288170132

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de


Kraftform Kompakt SH 1 PlumbKit, 25 pieces

Kraftform Kompakt user-specific sets




Set contents:


6000 Joker Ratcheting combination wrenches, 10 x 159 mm

	05073270001	1x	10 x 159 mm
	05073273001	1x	13 x 177 mm


8000 A Zyklop Speed Ratchet with 1/4" drive, 1/4" x 152 mm

	05003500001	1x	1/4" x 152 mm
---	-------------	----	---------------


8790 HMA Zyklop 1/4" socket, 7 x 23 mm

	05003506001	1x	7 x 23 mm
	05003509001	1x	10 x 23 mm
	05003512001	1x	13 x 23 mm

8784 A1 Zyklop bit adaptor, 1/4", 1/4" x 37 mm


	05003529001	1x	1/4" x 37 mm
---	-------------	----	--------------

867/4 TORX® HF Bits with holding function, TX 20 x 50 mm


	05060508001	2x	TX 20 x 50 mm
	05060509001	2x	TX 25 x 50 mm
	05060510001	1x	TX 30 x 50 mm
	05060511001 ¹⁾	1x	TX 40 x 50 mm

1) Pound-thru hexagonal; no Take it easy.

851/4 Z bits, PH 2 x 89 mm


	05059775001	1x	PH 2 x 89 mm
	05059760001	1x	PH 1 x 89 mm

840/4 Z bits, 3 x 89 mm

	05059630001	1x	3 x 89 mm
	05059631001	1x	4 x 89 mm
	05059632001	1x	5 x 89 mm
	05059633001 ¹⁾	1x	6 x 89 mm


1) Hexagonal blade

247 Single-pole phase tester, 0.5 x 3 x 70 mm


	05005655001 ¹⁾	1x	0.5 x 3 x 70 mm
---	---------------------------	----	-----------------

1) Product not available in the USA and Canada.

160 iS VDE Insulated screwdriver with reduced blade diameter for slotted screws, 0.6 x 3.5 x 100 mm

	05006440001	1x	0.6 x 3.5 x 100 mm
---	-------------	----	--------------------

160 i VDE Insulated screwdriver for slotted screws, 1 x 5.5 x 125 mm

	05006120001	1x	1 x 5.5 x 125 mm
---	-------------	----	------------------

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_user-specific_sets_kraftform_kompakt_sh_1.html

Wera - Kraftform Kompakt SH 1
05135927001 - 4013288170132

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Kompakt SH 1 PlumbKit, 25 pieces

Kraftform Kompakt user-specific sets



932 A Screwdriver for slotted screws, 1.2 x 7 x 125 mm



05018266001

1x 1.2 x 7 x 125 mm



395 H0 Nutdriver, 10 x 90 mm



05029465001

1x 10 x 90 mm

05029466001

1x 13 x 90 mm



Product not available in the USA and Canada.

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_user-specific_sets_kraftform_kompakt_sh_1.html

Wera - Kraftform Kompakt SH 1
05135927001 - 4013288170132

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de