

160 iSS/7 Screwdriver set Kraftform Plus Series 100. With reduced blade diameters and smaller handle diameters, 7 pieces
Kraftform Plus – Series 100 VDE



EAN:	4013288178640	Size:	230x115x35 mm
Part number:	05135961001	Weight:	432 g
Article number:	160 iSS/7	Country of origin:	CZ
		Customs tariff number:	82054000

- Kraftform screwdrivers with reduced blade diameter as well as partially with slim handle design
- Allows screwdriving even in confined situations
- Kraftform handle for fast and ergonomic screwdriving
- Low-lying screw and spring elements can be reached and actuated
- Safe work at a voltage of 1,000 volts, individually tested

7 Wera VDE iSS screwdrivers with reduced shaft diameter as well as partially slimmer handle design to enable work in confined working situations and to allow low-lying screw and spring elements to be reached and actuated; individually tested tools as per IEC 60900; individual testing in a water bath at 10,000 volts so as to ensure safe working at the permitted voltage of 1,000 volts. "Take it easy" Tool Finder: colour coding according to profile and size. The anti-roll feature prevents any bothersome rolling away at the workplace.



Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_plus_series_100_vde_160_iss_7.html


Wera - 160 iSS/7
05135961001 - 4013288178640

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

160 iSS/7 Screwdriver set Kraffform Plus Series 100. With reduced blade diameters and smaller handle diameters, 7 pieces
Kraffform Plus – Series 100 VDE




The super slim screwdrivers for Electricians



The super slim screwdrivers for installation jobs in particularly confined spaces. Not only do the blades have a reduced diameter, the handles also have a very slim design.

VDE-insulated screwdriver with reduced blade diameter



Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

PlusMinus screwdrivers



For the use in terminal blocks, control cabinets, switches, relays, sockets etc.

Individually tested




Our screwdrivers are tested for dielectric strength under a 10,000 volt load to make sure that their most important property, their insulation, has been exhaustively tested. Each individual Wera VDE screwdriver is subjected to this test to guarantee safe working up to 1,000 volts.

Impact strength test



Impact strength tested at -40°C, guaranteeing safety even under extreme conditions.

Multicomponent Kraffform handle




Wera produces the Kraffform handle out of several materials with different properties. A resistant plastic is used for the core which ensures that the blade is held securely even under high strain. A softer material is used for the coloured soft zones, which provides high frictional resistance and allows the transfer of high forces - resulting in less required screwdriving effort. The red sections with their hard surfaces prevent any "sticking" of the hand to the handle, making rapid repositioning of the hand possible.

Prevents hand injuries



The outstanding design of the Kraffform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

"Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraffform_plus_series_100_vde_160_iss_7.html

Wera - 160 iSS/7
 05135961001 - 4013288178640

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

160 iSS/7 Screwdriver set Kraftform Plus Series 100. With reduced blade diameters and smaller handle diameters, 7 pieces
Kraftform Plus – Series 100 VDE



Set contents:

160 iSS VDE Insulated screwdriver with reduced blade and handle diameter for slotted screws, 0.8 x 4 x 100 mm



05020129001 1x 0.8 x 4 x 100 mm



160 iS VDE Insulated screwdriver with reduced blade diameter for slotted screws, 1 x 5.5 x 125 mm



05006442001 1x 1 x 5.5 x 125 mm
05006440001 1x 0.6 x 3.5 x 100 mm



162 iSS PH VDE Insulated screwdriver with reduced blade diameter for Phillips screws, PH 1 x 80 mm



05020131001 1x PH 1 x 80 mm
05020133001 1x PH 2 x 100 mm



165 iSS PZ/S VDE Insulated screwdriver with reduced blade diameter for PlusMinus screws (Pozidriv/slotted), # 1 x 80 mm



05020132001 1x # 1 x 80 mm
05020134001 1x # 2 x 100 mm



Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_plus_series_100_vde_160_iss_7.html

Wera - 160 iSS/7
05135961001 - 4013288178640

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de