

Wera 2go E 1 Tool set for electricians, 73 pieces

Wera 2go




EAN: 4013288221278
Part number: 05134025001
Article number: Wera 2go E 1

Size: 370x345x140 mm
Weight: 7300 g
Country of origin: DE (05)
Customs tariff number: 82032000

- Extensive 73-piece tool set in the compact Wera 2go 2 tool container for electricians in mobile operations
- Premium brand tools by Wera, Jung, KNIPEX®, Lyra®, PICARD®, PUK® and Stabila®
- Wera Kraftform Kompakt Turbo i 1 (16-piece handle/interchangeable blades VDE set) for four times the screwdriving speed and Wera 8100 SA 6 Zyklus Speed ratchet set (1/4", 28-piece set)
- Joker 6004 S self-setting spanner for bolts and screws of 10-13mm (metric) and 7/16"-1/2" (imperial)
- With chiseldriver for screwdriving, chiselling, mortising as well as 4 VDE screwdrivers - 2 of which with stainless steel blade to prevent extraneous rust

Compact tool set with the 73 most important tools for electricians with products by Wera, Jung, KNIPEX®, Lyra®, PICARD®, PUK® and Stabila®. Mobility is made considerably easier thanks to the compact tool container from the Wera 2go system.



Web link
https://products.wera.de/en/wera_2go_wera_2go_e_1.html

Wera - Wera 2go E 1
05134025001 - 4013288221278


Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Fast movers




The Zyklop Speed ratchets are really fast movers. The gyrating mass design means that screwdriving is accelerated. The rotation-symmetric structure of the Kraftform handle and the free-turning sleeve reinforce this rapid twisting process, particularly when the ratchet does not engage due to too little resistance in the thread.

Joker 6004: Automatically and continuously self-setting



With its automatically and continuously gripping parallel jaws the Joker spanner 6004 covers all dimensions in the respective field of application. The tool automatically finds the required size when placed on the bolt or screw, no setting required.

Joker 6004: Small return angle



Thanks to the corner-width rectangular prisms, a return angle of only 30° can be achieved.

Web link

https://products.wera.de/en/wera_2go_wera_2go_e_1.html

Wera - Wera 2go E 1
05134025001 - 4013288221278

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Wera 2go

Joker 6004: Ratchet mechanism for fast work



The ratchet function in the open end sees to fast and consistent screwdriving without removing the tool.

Wera Stainless Steel Tools.



Solution to the rust problem: screwdriving stainless steel together with stainless steel! Wera stainless steel tools are manufactured out of stainless steel so unsightly rust can be avoided.

Kraftform Kompakt Turbo VDE



Many users would like to be able to carry out screwdriving processes faster without compromise. With a screwdriver that is precise, allows powerful screwdriving, and is much faster than a conventional screwdriver. A part-time universal gear is the solution: Integrated in the screwdriver handle, it quadruples the working speed with smooth couplings - purely mechanically. One hand holds the front part of the handle, the other hand turns the rear part of the handle. The turbo function can be switched on or off at the push of a button. Turning it off is recommended for tightening and loosening with high torque, e.g. for screw connections in wood, as well as for fine adjustments. Robust, maintenance-free gear made of steel with a maximum torque of 14 Nm when the turbo function is deactivated. With the Wera VDE interchangeable blades individually tested as per IEC 60900, the VDE version of the Kraftform Turbo hand holder 827 T i guarantees fast and safe working even in live environments (up to 1,000 volts).

L-keys with holding function for hexagon socket screws



The clamping of the screw is achieved by a flexible locking ball. The holding function is especially helpful in confined, hard-to-reach spaces, where there is no room for a second hand to secure the screw on the tool.

Web link

https://products.wera.de/en/wera_2go_wera_2go_e_1.html

Wera - Wera 2go E 1
05134025001 - 4013288221278

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Wera 2go E 1 Tool set for electricians, 73 pieces



Wera 2go

Set contents:

Wera 2go 2 Tool Container, 3 pieces

05004351001 1x 3 pieces



8100 SA 6 Zyklop Speed Ratchet Set, 1/4" drive, metric, 28 pieces



05004016001 1x 28 pieces



950/9 Hex-Plus Multicolour HF 1 L-key set, metric, BlackLaser, with holding function, 9 pieces



05022210001 1x 9 pieces



Kraftform Kompakt Turbo i 1, 16 pieces



05057484001¹⁾ 1x 16 pieces

¹⁾ Discontinued item



932 A Screwdriver for slotted screws, 1.2 x 7 x 125 mm



05018266001 1x 1.2 x 7 x 125 mm



3162 i PH VDE Insulated screwdriver for Phillips screws, stainless, PH 2 x 100 mm



05022734001 1x PH 2 x 100 mm



3165 i PZ VDE Insulated screwdriver for Pozidriv screws, stainless, PZ 2 x 100 mm



05022741001 1x PZ 2 x 100 mm



Web link

https://products.wera.de/en/wera_2go_wera_2go_e_1.html

Wera - Wera 2go E 1
05134025001 - 4013288221278

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Wera 2go E 1 Tool set for electricians, 73 pieces



Wera 2go

160 i VDE Insulated screwdriver for slotted screws, 1.2 x 6.5 x 150 mm



05006125001 1x 1.2 x 6.5 x 150 mm



160 iS VDE Insulated screwdriver with reduced blade diameter for slotted screws, 0.6 x 3.5 x 100 mm



05006440001 1x 0.6 x 3.5 x 100 mm



6004 Joker S Self-setting spanner, 10-13 x 7/16-1/2" x 154 mm

05020100001 1x 10-13 x 7/16-1/2" x 154 mm



KNIPEX® Combination pliers 160mm 01 06 160

1x KNIPEX® Combination pliers 160mm 01 06 160



KNIPEX® Diagonal insulation stripper 14 26 160

1x KNIPEX® Diagonal insulation stripper 14 26 160



KNIPEX Snipe nose pliers with blade (stork beak pliers) 26 16 200

1x KNIPEX Snipe nose pliers with blade (stork beak pliers) 26 16 200



KNIPEX® Cobra® VDE Hightech water pump pliers, insulated, 87 26 250

1x KNIPEX® Cobra® VDE Hightech water pump pliers, insulated, 87 26 250



KNIPEX® Cable knife 98 52

1x KNIPEX® Cable knife 98 52



KNIPEX® ErgoStrip® Universal dismantling tool 16 95 01

1x KNIPEX® ErgoStrip® Universal dismantling tool 16 95 01



PUK® 2200 Hand saw frame

1x PUK® 2200 Hand saw frame



Lyra® Construction marker DRY PROFI 4494202

1x Lyra® Construction marker DRY PROFI 4494202



Web link

https://products.wera.de/en/wera_2go_wera_2go_e_1.html

Wera - Wera 2go E 1
05134025001 - 4013288221278

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Wera 2go E 1 Tool set for electricians, 73 pieces



Wera 2go

STABILA® Spirit level Pocket Electric 17775

1x STABILA® Spirit level Pocket Electric 17775



STABILA® Spirit level type 70, 30 cm, 02281

1x STABILA® Spirit level type 70, 30 cm, 02281



STABILA® Wooden folding rule type 607, 2 m, yellow, 01104

1x STABILA® Wooden folding rule type 607, 2 m, yellow, 01104



PICARD® Fitter's hammer 400 g, German shape, 000101-0400

1x PICARD® Fitter's hammer 400 g, German shape, 000101-0400



Jung Plastering cup 127mm, 946 127 00

1x Jung Plastering cup 127mm, 946 127 00



Jung Scraping knife with natural wood handle, 922 050 00

1x Jung Scraping knife with natural wood handle, 922 050 00



Web link

https://products.wera.de/en/wera_2go_wera_2go_e_1.html

Wera - Wera 2go E 1

05134025001 - 4013288221278

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de