

867/4 IPR TORX PLUS® bits with bore hole, 10 IPR x 89 mm

Bits for Tamper-proof TORX PLUS® IPR Screws with Safety Pin



| | | | |
|------------------------|---------------|-------------------------------|-----------|
| EAN: | 4013288155665 | Size: | 89x7x6 mm |
| Part number: | 05134657001 | Weight: | 11 g |
| Article number: | 867/4 IPR | Country of origin: | CZ |
| | | Customs tariff number: | 82079030 |

- For recessed TORX PLUS® IPR screws with safety pin
- TORX PLUS® IPR bit with bore hole on the output side
- Tough for hard materials
- 1/4" hexagon drive (Wera connecting series 4)

High quality bits for recessed TORX PLUS® screws with safety pin. A 5-flank TORX PLUS® profile with bore hole. 1/4" hexagon, suitable for holders as per DIN ISO 1173-F 6.3.

Web link

https://products.wera.de/en/bits_holders_adaptors_and_sets_the_range_of_bits_bits_for_tamper-proof_torx_plus_ipr_screws_with_safety_pin_867_4_ipr.html

Wera - 867/4 IPR
05134657001 - 4013288155665

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Bits for Tamper-proof TORX PLUS® IPR Screws with Safety Pin

For recessed TORX PLUS® IPR screws with safety pin

Tough-absorbing bits







A 5-flank TORX PLUS® profile with a borehole. This drive geometry has only five flanks instead of the usual six and a borehole to protect safety screws against unauthorised unfastening. The screws cannot be turned with conventional, widely available tools.



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

Further versions in this product family:

| |  |  mm |  inch |  mm |
|--------------------|--|--|--|--|
| 05160821001 | 10 IPR | 50 | 2" | 4.0 |
| 05134657001 | 10 IPR | 89 | 3 1/2" | 4.0 |
| 05134654001 | 15 IPR | 50 | 2" | 4.0 |
| 05134720001 | 15 IPR | 89 | 3 1/2" | 4.0 |
| 05204126001 | 20 IPR | 50 | 2" | 4.5 |
| 05259135001 | 20 IPR | 89 | 3 1/2" | 4.5 |
| 05134655001 | 25 IPR | 50 | 2" | 6.0 |
| 05134722001 | 25 IPR | 89 | 3 1/2" | 6.0 |
| 05134656001 | 27 IPR | 50 | 2" | 6.0 |
| 05134658001 | 27 IPR | 89 | 3 1/2" | 6.0 |
| 05134732001 | 30 IPR | 50 | 2" | 6.0 |
| 05134723001 | 30 IPR | 89 | 3 1/2" | 6.0 |

Web link

https://products.wera.de/en/bits_holders_adaptors_and_sets_the_range_of_bits_bits_for_tamper-proof_torx_plus_ipr_screws_with_safety_pin_867_4_ipr.html

Wera - 867/4 IPR
05134657001 - 4013288155665

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de