

Kraftform Kompakt SH 2 PlumbKit, 15 pieces

Kraftform Kompakt user-specific sets



| | | | |
|------------------------|------------------------|-------------------------------|---------------|
| EAN: | 4013288204387 | Size: | 325x150x70 mm |
| Part number: | 05136026001 | Weight: | 1361 g |
| Article number: | Kraftform Kompakt SH 2 | Country of origin: | CZ |
| | | Customs tariff number: | 82054000 |

- 15 screwdriving tools for sanitary or heating applications in compact and robust Wera textile box
- JOKER combination ratcheting wrench with special holding plate against slipping/loss of the screw
- VDE-insulated Kraftform holder and interchangeable blades
- Kraftform Chiseldriver with hex blade extending through handle and integrated impact cap
- Hollow shaft nutspinner for nuts on protruding threaded rods

Compact tool set with 15 important screwdriving tools for the sanitary and heating sectors. With 2 Joker Switch ratcheting combination wrenches, VDE handle with 4 extra-slim blades, voltage tester, 4 L-keys with thermoplastic sleeve, chiseldriver and 2 Kraftform Plus nutspinners with hollow shaft. The details: 2 Joker Switch ratcheting combination wrenches with special retaining plate to prevent slipping/loss of the screw and more torque transfer; 1 VDE handle and 4 VDE iS blades for safe working at up to 1000 volts (iS with reduced blade diameter and integrated protective insulation for reaching and operating low-lying screw and spring elements); 1 single-pole phase tester 247; 4 L-keys with Hex-Plus profile to prevent rounding out screws; 1 Kraftform chiseldriver 932 A (slotted) with pound-thru hexagonal blade and integrated impact cap for screwdriving and light chiselling; 2 socket wrench nutspinners 395 HO with hollow shaft for tightening or loosening nuts on protruding threaded rods as well as fixed screws. Including tools with "Take it easy" tool finder with colour coding in accordance to profiles and size stamping - for fast and easy tool selection.



Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_user-specific_sets_kraftform_kompakt_sh_2.html

Wera - Kraftform Kompakt SH 2
05136026001 - 4013288204387

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Kompakt user-specific sets

Kraftform Kompakt SH 2 PlumbKit



Compact tool set with 15 important screwdriving tools for the sanitary and heating sectors.



Compact tool set with the 15 most important screwdriving tools for plumbing and heating applications.

Joker Ratcheting combination wrenches




The Joker's holding function means that nuts and bolts can be held in the jaw and easily positioned where they are needed. Fastening on to the thread can then be done quickly and safely, thanks to the innovative special stop-plate which holds the fastener. No more time-wasting searches for dropped nuts and bolts! After applying and positioning the nut or bolt, fastening can begin immediately - no additional tools required.

Series 900 – the Chiseldriver



The chiseldriver is the solution for jobs that require more than just screwdriving. For fastening, chiselling and loosening seized screws or hose clamps. With an integrated impact cap that extends service life and reduces the risk of splintering. With a pound-thru hexagon blade made from high-grade material for - zero-loss transfer of high forces when struck with a hammer. The tough viscous tempered material prevents the blade from splintering or breaking. More TORQUE can be transferred by attaching an open-jawed or ring spanner to the integrated hexagon bolster.

Hollow shaft nutsetter




A screwdriver with a hollow shaft is needed whenever there are screwdriving jobs involving threaded rods i.e. the threaded rod through the nut can slip into the hollow shaft of the screwdriver.

Handle/interchangeable blade system – Kraftform Kompakt VDE



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

VDE interchangeable blade with reduced shaft diameter



Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_user-specific_sets_kraftform_kompakt_sh_2.html

Wera - Kraftform Kompakt SH 2
05136026001 - 4013288204387

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Kompakt SH 2 PlumbKit, 15 pieces

Kraftform Kompakt user-specific sets

Set contents:

395 HO Nutdriver, 10 x 90 mm



| | | |
|-------------|----|------------|
| 05029465001 | 1x | 10 x 90 mm |
| 05029466001 | 1x | 13 x 90 mm |

932 A Screwdriver for slotted screws, 1.2 x 7 x 125 mm



| | | |
|-------------|----|------------------|
| 05018266001 | 1x | 1.2 x 7 x 125 mm |
|-------------|----|------------------|

6001 Joker Switch Ratcheting combination wrench, with switch lever, 10 x 159 mm



| | | |
|-------------|----|-------------|
| 05020065001 | 1x | 10 x 159 mm |
| 05020068001 | 1x | 13 x 179 mm |

950 SPKL HF L-key Multicolour, metric, with holding function, 3 x 123 mm



| | | |
|-------------|----|------------|
| 05022200001 | 1x | 3 x 123 mm |
| 05022201001 | 1x | 4 x 137 mm |
| 05022202001 | 1x | 5 x 154 mm |
| 05022203001 | 1x | 6 x 172 mm |

817 VDE Kraftform blade-holding handle, 9 x 98 mm



| | | |
|-------------|----|-----------|
| 05003990001 | 1x | 9 x 98 mm |
|-------------|----|-----------|



Kraftform Kompakt VDE 62 iS, PH 1 x 154 mm



| | | |
|---------------------------|----|---------------|
| 05003413001 ¹⁾ | 1x | PH 1 x 154 mm |
| 05003414001 ¹⁾ | 1x | PH 2 x 154 mm |

1) Discontinued item

Kraftform Kompakt VDE 60 iS, 0.6 x 3.5 x 154 mm



| | | |
|---------------------------|----|--------------------|
| 05003406001 ¹⁾ | 1x | 0.6 x 3.5 x 154 mm |
| 05003408001 ¹⁾ | 1x | 1 x 5.5 x 154 mm |

1) Discontinued item

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_user-specific_sets_kraftform_kompakt_sh_2.html

Wera - Kraftform Kompakt SH 2
05136026001 - 4013288204387

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Kompakt SH 2 PlumbKit, 15 pieces

Kraftform Kompakt user-specific sets



247 Single-pole phase tester, 0.5 x 3 x 70 mm



05005655001¹⁾

1x 0.5 x 3 x 70 mm

1) Product not available in the USA and Canada.



Hook and Loop Fastener Strip 240, 50 x 240 mm

1x 50 x 240 mm



Product not available in the USA and Canada.

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_user-specific_sets_kraftform_kompakt_sh_2.html

Wera - Kraftform Kompakt SH 2
05136026001 - 4013288204387

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de