

Kraftform Plus – Series 100 VDE



EAN:	4013288122957	Size:	285x210x55 mm
Part number:	05347777001	Weight:	632 g
Article number:	160 i/168 i/6 Rack	Country of origin:	CZ
		Customs tariff number:	82054000

- Insulated blades for secure work at 1,000 volts
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Take it easy tool finder: colour coding according to profile and size
- Hexagonal anti-roll feature against rolling away
- Black Point tip for enhanced corrosion protection and an exact fit

6-piece screwdriver set with individually tested, insulated screwdrivers as per IEC 60900. Individual testing in a water bath at 10,000 volts so as to ensure safe working at the permitted voltage of 1,000 volts. Kraftform Plus handle for pleasant, ergonomic working that makes blisters and calluses a thing of the past. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Partially Lasertip: the tip literally bites itself into the screw head and prevents any slipping. "Take it easy" Tool Finder: colour coding according to profile and size. The anti-roll feature prevents any bothersome rolling away at the workplace. Including a rack for storage.

Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_plus_series_100_vde_160_i_168_i_6 Rack.html

Wera - 160 i/168 i/6 Rack
05347777001 - 4013288122957

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraffform Plus – Series 100 VDE

Individually tested



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.



Our screwdrivers are tested for dielectric strength under a 10,000 volt load to make sure that their most important property, their insulation, has been exhaustively tested. Each individual Wera VDE screwdriver is subjected to this test to guarantee safe working up to 1,000 volts.

Impact strength test



Impact strength tested at -40°C, guaranteeing safety even under extreme conditions.

Lasertip




A precisely-focused laser creates a sharp-edged surface structure. Wera Lasertip "bites" itself into the screw head and prevents any slips out of the recess. It is available for screwdrivers for slotted, Phillips and Pozidriv screws.

Reduced contact pressure




Wera Lasertip reduces the contact pressure required and enhances force transfer - meaning less screwdriving effort is required. Screwdriving becomes safer and easier.

"Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Multicomponent Kraffform handle



Wera produces the Kraffform handle out of several materials with different properties. A resistant plastic is used for the core which ensures that the blade is held securely even under high strain. A softer material is used for the coloured soft zones, which provides high frictional resistance and allows the transfer of high forces - resulting in less required screwdriving effort. The red sections with their hard surfaces prevent any "sticking" of the hand to the handle, making rapid repositioning of the hand possible.

Non-roll feature



The hexagonal non-roll feature prevents any rolling away at the workplace.

Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraffform_plus_series_100_vde_160_i_168_i_6_rack.html



Wera - 160 i/168 i/6 Rack
05347777001 - 4013288122957

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de



Kraffform Plus – Series 100 VDE

Set contents:

162 i PH VDE Insulated screwdriver for Phillips screws, PH 1 x 80 mm



	05006152001	1x	PH 1 x 80 mm
	05006154001	1x	PH 2 x 100 mm

160 i VDE Insulated screwdriver for slotted screws, 0.6 x 3.5 x 100 mm

	05006110001 ¹⁾	1x	0.6 x 3.5 x 100 mm
	05006120001	1x	1 x 5.5 x 125 mm

1) without Lasertip

168 i VDE Insulated screwdriver for square socket head screws, # 1 x 80 mm

	05004780001	1x	# 1 x 80 mm
	05004781001	1x	# 2 x 100 mm

Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraffform_plus_series_100_vde_160_i_168_i_6_rack.html

Wera - 160 i/168 i/6 Rack
05347777001 - 4013288122957

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de