


TECHNICAL DATA SHEET

SECUMAX 145 NO. 145001

Safety technology



Concealed blade – a maximum degree of safety

The SECUMAX 145 blade is not an open one, but is hidden from people and goods. This provides you with a maximum degree of safety from cut injuries and from damage to goods.



SMALL SAFETY KNIFE WITH CONCEALED BLADE FOR VARIOUS CUTTING MATERIALS.

Order No. 145001.12

Compact design. Powerful performance.

The SECUMAX 145 is our clever, compact safety knife for routine cutting tasks. The glass-fibre reinforced plastic handle and 0.5 mm strong blade gives it remarkable robustness. At just 12 g it is also extremely light. The disposable cutting tool easily copes with single-layer cardboard, film and packing tape, for example. The two cutting edges are safely concealed to protect fingers.

2 in 1 blade head

The blade head provides two functions: cutting and piercing. Use the knife's noses to the left and right of the blade to effortlessly pierce materials (e.g. card and film), and the blade head's corners for packing tape.

Concealed blade

With a 4 mm blade access, the blade is highly concealed. Out of reach for fingers but accessible to the materials to be cut. And contents under the cutting surface will also be kept safe from contact with the cutting edge.

Flat and robust design

It is not just the handle that has an extremely flat design – the cutting channel too measures just 1.5 mm, requiring less effort for cutting. The tool also retains its strength – thanks to a 0.5 mm blade and high-quality plastic.




Light and easy

The SECUMAX 145 is so lightweight that users will hardly notice it. This is aided by the comfortably rounded handle at just 4 mm wide, and thumbs will intuitively find their place at the ergonomically designed grooves.

Clever guide surfaces

A tip from us on cutting card: hold the blade at an angle to improve cutting! It is no accident that the guide surfaces are located at the front of the knife – they aid cutting at the most effective angle.

USAGE



PRODUCT FEATURES

Technical features



Maximum safety



Disposable knife



Abrasion resistant



Ergonomic



2-times usable blade



Cutting depth



For right and left hander



Lanyard hole



Printable for promotional purposes

Main cutting materials



Cardboard: 1-ply



Wrapping, stretch, and shrink foil



Tape



Bagged goods



Layers of foil or paper



Yarn, cord

Installed blade

Blade thickness 0.50 mm.

BLADE CHANGE

The blade is moulded into the body of the knife and cannot be changed.

Blade thickness 0.50 mm.

SERVICES OFFERED



Safety poster



Training video



Technical data sheet



Consulting service

PRODUCT AND PACKAGING DETAILS

Order No.	NO. 145001.12	Packaging unit (PU)	10 in box (loose)
Knife size (L x W x H)	118 x 4 x 35.4 mm	Weight PU	136.0 g
Weight knife	12.0 g	EAN Code (PU)	4002632800658
Basic material	Glass fibre reinforced plastic	Customs tariff number	82119300
Cutting depth	3.8 mm		

SAFETY CERTIFICATE

Date of issue	10.05.2016
Certification	GS certificate NO. 602578-6075-55094-2016 C

Certificates and awards



ENVIRONMENT

This SECUMAX 145 corresponds with the current REACH ordinance.

SECURITY ADVICE

To ensure that you use your new MARTOR knife safely and most effectively, please read and note the following user instructions. Please keep the written guide in a safe place so that you can access it at any time.

1. Usage advice: Please use the product carefully for described work only and not for any purposes other than those that are intended. Please take the correct handling and the proper use of the cutting tool into account in this regard.

2. Special application Instructions to avoid the danger of injuries: Only use cutting tools that are in perfect condition and have sharp, clean and undamaged blades. Employ the utmost care when handling the knives. CAUTION: The blade is sharp and can result in serious and deep cuts. Therefore, never reach into the blade! To reduce the danger of injuries, hold the hand that is being used to restrain and stabilise the

cutting base in such a manner that the restraining hand or even other body parts are not endangered in the event that the knife slips. Do not modify this product in any way. Modifications of any kind may impair product safety. CAUTION: The risk of injury caused by manipulation of this product is extremely high. When both cutting edges are no longer sharp, dispose of the knife as general waste.

3. Non-use of the knife: Store the knife in a secure place.

4. Care instructions: Always keep the knife clean and do not expose it to unnecessary humidity to safeguard a long service life.

CAUTION: No liability will be assumed for consequential losses. Subject to technical changes and errors! This knife does not belong in the hands of children!

ACCESSORIES

BELT HOLSTER S WITH CLIP NO. 9920



What do you do with your cutting tools when you are not actually using them? The MARTOR BELT HOLSTER S is a robust holder that allows you to carry all compact MARTOR cutters as well as our safety scissors at all times. In addition, the compartments are designed to allow you to load different tools: for example you can also carry a pen or a pack of blades. The MARTOR BELT HOLSTER is the ideal place to stow your tools safely when moving from A to B - and have them at hand, as soon as they are required.

MANUFACTURER

MARTOR KG | Lindgesfeld 28 | 42653 Solingen | Germany
T +49 212 73870-0 | info@martor.de | www.martor.com