

## Product data sheet uvex 2 construction 6513 1-3 S3 SRC

**UVEX ARBEITSSCHUTZ GmbH, Würzburger Str. 181-189, D-90766 Fürth**

<b>General features</b>	<ul style="list-style-type: none"><li>• Robust, lightweight and modern S3 lace-up safety boot with wide fit</li><li>• All sole materials are free of silicone, plasticizers and other substances that interfere with wetting agents</li><li>• Dirt-resistant, smooth-running and heat-resistant lacing system</li></ul>
<b>Protection features</b>	<ul style="list-style-type: none"><li>• Water-repellent leather with uvex waterstop technology for reliable protection against splashing water</li><li>• Penetration-resistant steel midsole</li><li>• Anatomical shaped, moulded polyurethane heel basket for stability and protection against ankle twisting</li><li>• 100% metal-free uvex xenova safety toe cap – compact design, anatomical shape, good lateral stability and no thermal conductivity</li><li>• Reflective side strips for optimum visibility</li><li>• Secure grip when climbing on ladders due to the stabilizing arch support</li></ul>
<b>Comfort features</b>	<ul style="list-style-type: none"><li>• Outstanding wearer comfort thanks to a newly developed last and climate-optimised, breathable materials</li><li>• Virtually seam-free construction made from water-repellent leather to eliminate pressure points</li><li>• Removable anti-static comfortable insole with a moisture transport system and additional shock absorption around the heel and forefoot</li><li>• Sizes 35 to 40 have been produced using a women's last</li></ul>
<b>Outsole</b>	<ul style="list-style-type: none"><li>• Ergonomically designed dual-density polyurethane</li></ul>

	<p>outsole with deep, self-cleaning tread and excellent slip resistance</p> <ul style="list-style-type: none"> <li>• Excellent cushioning and extremely flexible</li> <li>• Resistant to oil and petrol</li> <li>• Resistant to temperatures for short periods up to +120°C</li> </ul>																
<b>Certificates</b>	<ul style="list-style-type: none"> <li>• Certified with uvex medicare for individual, orthopedic inlay soles and individual adjustments of the sole unit such as overall increase, inside and outside increase and other solutions.</li> </ul>																
<b>Areas of application</b>	<ul style="list-style-type: none"> <li>• Medium application</li> </ul>																
<b>Technical data</b>	<p>uvex 2 construction safety boot S3 SRC</p> <table> <tr> <td>Art.-no.</td> <td>6513 1</td> <td>2</td> <td>3</td> </tr> <tr> <td>Width</td> <td>10</td> <td>11</td> <td>12</td> </tr> <tr> <td>Size</td> <td colspan="3">35-52</td> </tr> <tr> <td>Standard</td> <td colspan="3">EN ISO 20345:2011 S3 SRC</td> </tr> </table>	Art.-no.	6513 1	2	3	Width	10	11	12	Size	35-52			Standard	EN ISO 20345:2011 S3 SRC		
Art.-no.	6513 1	2	3														
Width	10	11	12														
Size	35-52																
Standard	EN ISO 20345:2011 S3 SRC																
<b>Accessories</b>	<p><i>Removable uvex 2 comfortable climatic insole</i> (Article-No.: 9534 7-9)</p> <ul style="list-style-type: none"> <li>• improved full-surface shock absorption</li> <li>• ultra-breathable, moisture-absorbing and quick-drying materials</li> <li>• shock absorption zones support natural movement of the foot</li> <li>• non-irritating, comfortable surface structure</li> <li>• anti-static properties</li> <li>• arch support</li> </ul> <p><i>Laces</i></p> <ul style="list-style-type: none"> <li>• black (Article-No.: 9599.9 11)</li> </ul>																