

Product data sheet uvex 3 6874 1-3 S3 CI SRC

**UVEX ARBEITSSCHUTZ GmbH, Würzburger Str. 181-189, D-90766 Fürth**

General features	<ul style="list-style-type: none">• Robust, lightweight and modern S3 lace-up safety boot with wide fit• All sole materials are free of silicone, plasticizers and other substances that interfere with wetting agents• Dirt-resistant and smooth-running lacing system
Protection features	<ul style="list-style-type: none">• Water-repellent leather with uvex waterstop technology for reliable protection against splashing water• Innovative uvex bionom x design creates a biomechanical symbiosis between the foot, the upper, the sole and the floor• uvex anklePro extremely shock-absorbent ankle foam provides protection against painful impacts• uvex lacelock fastening hook for a secure hold and more stability when lacing up the shoe• new, innovative uvex i-PUREnrj sole technology provides outstanding shock-absorption properties at the forefoot and the heel, excellent rebound energy over the entire midsole and high levels of stability thanks to the foam heel basket• Penetration-resistant, non-metallic midsole in accordance with the current safety standards, does not restrict the flexibility of the shoe• 100% metal-free uvex xenova safety toe cap – compact design, anatomical shape, good lateral stability and no thermal conductivity• Reflective elements for optimum visibility• Secure grip when climbing on ladders due to the stabilizing arch support

	<ul style="list-style-type: none"> Meets the ESD specification with volume resistance under 35 megaohms 																
Comfort features	<ul style="list-style-type: none"> Outstanding wearer comfort thanks to a newly developed last and climate-optimised, breathable materials Virtually seam-free construction made from water-repellent leather to eliminate pressure points Removable anti-static comfortable insole with a moisture transport system and additional shock absorption around the heel and forefoot Soft padding on dust tongue and collar insert made from perforated leather 																
Outsole	<ul style="list-style-type: none"> Ergonomically designed dual-density polyurethane outsole with deep, self-cleaning tread and excellent slip resistance Excellent cushioning and extremely flexible Resistant to oil and petrol Resistant to temperatures for short periods up to +120°C 																
Certificates	<ul style="list-style-type: none"> Certified with uvex medicare for individual, orthopedic inlay soles and individual adjustments of the sole unit such as overall increase, inside and outside increase and other solutions. 																
Areas of application	<ul style="list-style-type: none"> heavy application 																
Technical data	<p>uvex 3 safety boot S3 CI SRC</p> <table> <tr> <td>Art.-no.</td> <td>6874 1</td> <td>2</td> <td>3</td> </tr> <tr> <td>Width</td> <td>10</td> <td>11</td> <td>12</td> </tr> <tr> <td>Size</td> <td colspan="3">38-52</td> </tr> <tr> <td>Standard</td> <td colspan="3">EN ISO 20345:2011 S3 CI SRC</td> </tr> </table>	Art.-no.	6874 1	2	3	Width	10	11	12	Size	38-52			Standard	EN ISO 20345:2011 S3 CI SRC		
Art.-no.	6874 1	2	3														
Width	10	11	12														
Size	38-52																
Standard	EN ISO 20345:2011 S3 CI SRC																
Accessories	<p><i>Removable uvex 3 comfortable climatic insole</i> (Article-No.: 9490 7-0)</p> <ul style="list-style-type: none"> improved full-surface shock absorption ultra-breathable, moisture-absorbing and quick-drying materials shock absorption zones support natural movement of the foot non-irritating, comfortable surface structure anti-static properties arch support <p><i>Laces</i></p> <ul style="list-style-type: none"> black (Article-No.: 9599.9 11) 																