

Product Datasheet uvex 1 6565.7-9 S1 SRC

**UVEX ARBEITSSCHUTZ GmbH, Würzburger Str. 181-189, D-90766 Fürth**

General features	<ul style="list-style-type: none">• Sporty, multifunctional safety shoe• Especially lightweight and flexible• Breathable high-tech micro velour upper material• Suitable for people allergic to chrome. Made from synthetic materials• All sole materials are free of silicones, plasticisers and other paint wetting impairment substances• BOA® Fit System for a fast, effortless, precision fit
Protection features	<ul style="list-style-type: none">• 100% metal-free uvex xenova® toe cap - compact design, anatomical shape, good lateral stability, no thermal conductivity properties• Meets the ESD specification with volume resistance less than 35 megaohms
Comfort features	<ul style="list-style-type: none">• Outstanding wearer comfort results from a newly developed last and climate-optimised, breathable materials• Virtually seamless design to eliminate pressure points• Removable comfort insole, antistatic, with moisture control system and additional shock absorption in the heel and at the front of the foot• Distance mesh lining provides optimum breathability• Soft padded collar and tongue
Outsole	<ul style="list-style-type: none">• PUR outsole, non-marking

	<ul style="list-style-type: none"> • Ergonomically designed tread • Multi-layer-shock absorption system using dual density polyurethane for walking comfort • Excellent slip resistance • Self-cleaning tread • Resistant to oil and petrol 																				
Certificates	<ul style="list-style-type: none"> • Certified with uvex medicare for individual, orthopaedic inlay soles and individual adjustments of the sole unit such as overall increase, inside and outside increase and other solutions. 																				
Areas of application	<ul style="list-style-type: none"> • Light applications 																				
Technical data	<table> <tr> <td>Art.-no.</td> <td>6565</td> <td>.7</td> <td>.8</td> <td>.9</td> </tr> <tr> <td>Width</td> <td></td> <td>10</td> <td>11</td> <td>12</td> </tr> <tr> <td>Standard</td> <td colspan="4">EN ISO 20345:2011 S1 SRC</td> </tr> <tr> <td>Size</td> <td colspan="4">35 – 52</td> </tr> </table>	Art.-no.	6565	.7	.8	.9	Width		10	11	12	Standard	EN ISO 20345:2011 S1 SRC				Size	35 – 52			
Art.-no.	6565	.7	.8	.9																	
Width		10	11	12																	
Standard	EN ISO 20345:2011 S1 SRC																				
Size	35 – 52																				
Accessories	<p><i>uvex 1 comfortable climatic insole</i> (article no.: 9534.7-9)</p> <ul style="list-style-type: none"> • Provides the foot with exceptional, full-surface shock absorption and ensures comfort in high-strain zones • Ultra breathable and moisture-absorbing materials • Shock absorption zones that assist natural movement • Non-irritating, comfortable surface structure 																				