

Product Datasheet uvex 2 6503.1-4 S3 SRC

**UVEX ARBEITSSCHUTZ GmbH, Würzburger Str. 181-189, D-90766 Fürth****Product information**

- Sporty, multifunctional safety boot
- Extremely light and flexible
- The latest generation of 100% metal-free uvex xenova® toe cap. Compact design, anatomical shape, good side and ankle twist stability, no thermal conductivity and antimagnetic properties
- Metal-free, penetration-resistance insole in accordance with the latest standard, which does not impact shoe flexibility
- Made with new high-performance technology for exceptional wearer comfort
- uvex climazone technology for optimum comfort
- Water-repellent, breathable and extremely soft leather upper
- Distance mesh lining provides optimum breathability
- Virtually seam-free construction to eliminate pressure points
- Removable comfort insole, antistatic, with moisture control system and additional shock absorption in the heel and at the front of the foot
- Soft, padded collar and padded tongue
- Injection-moulded polyurethane scuffcap to protect upper leather on toe cap and significantly extend resistance time
- Meets ESD requirements: resistance to ground < 35

	<p>megaohm</p> <ul style="list-style-type: none"> • Certified with uvex medicare for individual, orthopaedic inlay soles and individual adjustments of the sole unit such as overall increase, inside and outside increase and other solutions 																				
Outsole	<ul style="list-style-type: none"> • Lightweight two-layer insole with excellent shock absorption characteristics and outstanding slip resistance, free of lacquer wetting inhibitors such as silicones and phthalates (plasticisers) • Multilayer shock absorption system comprising double-layer uvex 2 PU outsole and comfortable insole, shock absorption in the front and heel: all this protects the musculoskeletal system, even over long periods of time • Optimised ankle protection to ensure safety when working on ladders • Particularly abrasion-resistant TPU sections ensure secure stepping and rolling of foot, which helps prevent accidents • Rugged, self-cleaning sole ridges ensures maximum grip for demanding applications on uneven or dirty floors (SRC labelling). 																				
Technical Data	<table> <tr> <td>Art.-no.</td> <td>6503.1</td> <td>.2</td> <td>.3</td> <td>.4</td> </tr> <tr> <td>Fitting</td> <td>10</td> <td>11</td> <td>12</td> <td>14</td> </tr> <tr> <td>Standard</td> <td colspan="4">EN ISO 20345:2011 S3 SRC</td> </tr> <tr> <td>Size</td> <td colspan="4">35 – 52</td> </tr> </table>	Art.-no.	6503.1	.2	.3	.4	Fitting	10	11	12	14	Standard	EN ISO 20345:2011 S3 SRC				Size	35 – 52			
Art.-no.	6503.1	.2	.3	.4																	
Fitting	10	11	12	14																	
Standard	EN ISO 20345:2011 S3 SRC																				
Size	35 – 52																				
Accessories	<p><i>uvex 1 comfortable climatic insole</i> (article no.: 9534.7-9 + .0)</p> <ul style="list-style-type: none"> • Provides the foot with exceptional, full-surface shock absorption and ensures comfort in high-strain zones • Ultra breathable and moisture-absorbing materials • Shock absorption zones that assist natural movement • Non-irritating, comfortable surface structure <p><i>Laces</i></p> <ul style="list-style-type: none"> • Black (article no.: 9599.9 11) 																				