

Product data sheet uvex 2 trend 6935.1 - .3 / .7 - .9 S3 / S2 SRC



UVEX ARBEITSSCHUTZ GmbH, Würzburger Str. 181-189, D-90766 Fürth

General features	<ul style="list-style-type: none">• Sporty S2 / S3 safety boot with wide fit• Water repellent leather• Smooth-running, dirt- and heat-resistant lacing system• Foamed polyurethane scuffcap helps increase product life of upper (S3 models)• All sole materials are free of silicones, plasticisers and other paint wetting impairment substances
Protection features	<ul style="list-style-type: none">• Meets the ESD specification with volume resistance less than 35 megaohms• Penetration resistant steel midsole (S3 models) and steel toe cap• Ergonomically designed outsole with excellent slip resistance• Stabilising uvex anti-twist heel cap to prevent ankle twisting• Reflective details for enhanced visibility
Comfort features	<ul style="list-style-type: none">• Soft padding on collar and tongue• Removable antistatic comfortable insole, with a moisture transport system and additional shock absorption around the heel and forefoot
Outsole	<ul style="list-style-type: none">• PUR outsole, non-marking• Ergonomically designed tread• Two-layer system with abrasion-resistant outsole

	<p>guarantees excellent walking comfort</p> <ul style="list-style-type: none"> • Excellent slip resistance • Self-cleaning tread • Resistant to oil and petrol • Resistant to temperatures for short periods up to ca. +120°C 																												
Certificates	<ul style="list-style-type: none"> • Certified with uvex medicare for individual, orthopaedic inlay soles and individual adjustments of the sole unit such as overall increase, inside and outside increase and other solutions. 																												
Areas of application	<ul style="list-style-type: none"> • Medium applications 																												
Technical data	<table> <tr> <td>Art.-No.</td> <td>6935.1</td> <td>.2</td> <td>.3</td> </tr> <tr> <td>Width</td> <td>10</td> <td>11</td> <td>12</td> </tr> <tr> <td>Standard</td> <td colspan="3">EN ISO 20345:2011 S3 SRC</td> </tr> <tr> <td>Art.-No.</td> <td>6935.7</td> <td>.8</td> <td>.8</td> </tr> <tr> <td>Width</td> <td>10</td> <td>11</td> <td>12</td> </tr> <tr> <td>Standard</td> <td colspan="3">EN ISO 20345:2011 S2 SRC</td> </tr> <tr> <td>Size</td> <td colspan="3">36 – 52</td> </tr> </table>	Art.-No.	6935.1	.2	.3	Width	10	11	12	Standard	EN ISO 20345:2011 S3 SRC			Art.-No.	6935.7	.8	.8	Width	10	11	12	Standard	EN ISO 20345:2011 S2 SRC			Size	36 – 52		
Art.-No.	6935.1	.2	.3																										
Width	10	11	12																										
Standard	EN ISO 20345:2011 S3 SRC																												
Art.-No.	6935.7	.8	.8																										
Width	10	11	12																										
Standard	EN ISO 20345:2011 S2 SRC																												
Size	36 – 52																												
Accessories	<p><i>comfortable climatic insole</i> (Article-No.: 9518.7-.9)</p> <ul style="list-style-type: none"> • Provides the foot with exceptional, full-surface shock absorption and ensures comfort in high-strain zones • Ultra breathable and moisture-absorbing materials • Shock absorption zones that assist natural movement • Non-irritating, comfortable surface structure <p><i>Laces</i></p> <ul style="list-style-type: none"> • Black (article no.: 8446.0.14) 																												