


uvex protection perfect multi function

Internal arc, heat, flame and chemical protection



trousers	uvex multi function	
model-no.:	3855	
colour:	royal blue, dark grey, dark blue, black	
material:	inherently flame retardant 49 % PPAN-FR, 42 % cotton, 5 % para-aramid, 3 % polyamide, 1 % carbon, approx. 300 g/m ²	
sizes:	42–64, 90–110	
article-no.:	17245	Royal blue
	17246	Dark grey
	17247	Dark blue
	17248	black
Sales unit:	1 pcs.	

PPE-category III

EN ISO 11611:2015



class 1 - A1

EN 1149-5:2018



EN 13034:2005+A1:2009



Type 6

EN ISO 11612:2015



A1,B1,C1,E2,F1

IEC 61482-2:2018



APC 1



INDUSTRIALWASH ●●

Product description:

Multifunctional trousers with ergonomic fit, the wide range of challenges arises (e.g. handling chemicals or low risk liquid iron - code E2).

- stretch inserts at knee for best mobility and reflective pipings
- adjustable elastic tape at waistband
- 1 back pocket with velcro tape
- 1 loose hanging ruler pocket with velcro tape closure
- 1 cargo pocket with velcro tape closure
- flame retardent reflective stripe around the leg
- knee pockets inside


Note: This protective clothing must always be worn as a suit jacket in combination with dungarees / trousers and closed!

The declaration of conformity for this product can be viewed at: uvex-safety.com/ce

Pay attention to the user information!

uvex protection perfect multi function

Internal arc, heat, flame and chemical protection



dungaree	uvex multi function	
model-no.:	3661	
colour:	royal blue, dark grey, dark blue, black	
material:	inherently flame retardant 49 % PPAN-FR, 42 % cotton, 5 % para-aramid, 3 % polyamide, 1 % carbon, approx. 300 g/m ²	
sizes:	40/42 – 64/66, 90/94 – 106/110	
article-no.:	17251	Royal blue
	17252	Dark grey
	17253	Dark blue
	17254	black
Sales unit:	1 pcs.	

PPE-category III

EN ISO 11611:2015



class 1 - A1

EN 1149-5:2018



Type 6

EN ISO 11612:2015



A1, B1, C1, E2, F1

IEC 61482-2:2018



APC 1

EN 13034:2005+A1:2009



Product description:

Multifunctional dungarees with ergonomic fit, the wide range of challenges arises (e.g. handling chemicals or low risk liquid iron - code E2).

- stretch inserts at knee for best mobility and reflective pipings
- adjustable elastic tape at waistband
- 1 back pocket , 1 loose hanging ruler pocket, 1 cargo pocket, 1 flap pocket (all with velcro tape closure)
- flame retardant reflective stripe around the leg
- knee pockets inside
- elastic straps

Notes: This protective clothing must always be worn as a suit jacket in combination with dungarees / trousers and closed!

The declaration of conformity for this product can be viewed at: uvex-safety.com/ce

Pay attention to the user information!

uvex protection perfect multi function

Internal arc, heat, flame and chemical protection

model-no: 4792

article-no.:	17241	royal blue
	17242	dark grey
	17243	dark blue
	17244	black



model-no: 3855

article-no.:	17245	royal blue
	17246	dark grey
	17247	dark blue
	17248	black

model-no: 3661

article-no.:	17251	royal blue
	17252	dark grey
	17253	dark blue
	17254	black



Note:

This protective clothing must always be worn as a suit jacket in combination with dungarees / trousers and be closed!

Pay attention to the user information!