KERN **DB 500-2**

Convenient way to test the torque of tools





Category

Brand	Sauter
Product categoriy	Torque measuring device
Product group	Torquemeter for Tools
Product family	DB

Measuring System

Units	Nm, kgf/cm, kgf/m, in/ lbs, ft/lbs
Tolerance (% of [Max])	0,5%
Measuring range torque [Min]	25 Nm
Measuring range torque [Max]	500 Nm
Readability torque [d] (Nm)	0,1 Nm
Supported torque pickups	3/4 "
Overload protection (% of [Max])	120%
Internal data memory: Number of value groups	1
Internal data memory: Number of individual values	500
Internal measuring frequency	1000 Hz

Approval

Display	
Display type	LCD graphic
Display resolution	128×64

Construction	
Dimension (W×D×H)	200×100×50 mm
Dimensions device (W×D×H)	200×100×50 mm
Dimension housing (W×D×H)	180×110×45 mm

1

Material housing Functions Auto-off interval(s) in battery mode/rechargeable battery mode Peak function Limit-setting function	metal, lacquered
Auto-off interval(s) in battery mode/rechargeable battery mode Peak function	1 60 min
mode/rechargeable battery mode Peak function	1 60 min
	1 - 00 11111
Limit-setting function	\checkmark
	\checkmark
Memory function	\checkmark
Interfaces	RS-232 standard USB-Device
Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V
Input voltage device / power [Max]	9 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Battery & Power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Rechargeable battery charging time	14 h
Rechargeable battery operating time - backlight off	18 h
Battery / accumulator type	NiMH
Battery connection	2-pole tub connector
Battery capacity	750 mAh
Battery voltage	4,8 V
Environmental conditions	
Ambient temperature [Min]	15 °C
Ambient temperature [Max]	35 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C
Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	370×325×115 mm
Net weight	3,823 kg
Shipping method	Parcel service
	4,0 kg
Net weight approx.	

KERN **DB 500-2**

Convenient way to test the torque of tools



Shipping weight4,787 kgServices (optional)Article number for factory
calibration961-120Pictograms

STANDARD





OPTION

