KERN FH 5KUK



Universal digital force gauge for tensile and compressive force measurements with external load cell, with plug-in power supply for UK



Category	
Brand	Sauter
Product categoriy	Force measurement
Product group	Digital force gauge (external measuring cell)
Product family	FH-M

Measuring System	
Default unit	kN
Tolerance (% of [Max])	0,5%
Measuring range force [Max] (N)	5 kN
Readability force [d] (N)	1 N
Directions of force	tension compression
Measuring head measuring frequency	2 kHz
Number of platforms / channels	1
Overload protection (% of [Max])	150%
Internal data memory: Number of value groups	1
Internal data memory: Number of individual values	10

Approval	
CE mark	✓
Display	
Display type	LCD
Display digit height	10 mm
Screen reversible	✓

Construction	
Dimension display device (W×D×H)	230×66×36 mm
Dimension housing (W×D×H)	230×66×36 mm
Dimensions completely mounted (W×D×H)	230×66×36 mm
Material display housing	Plastics
Cable length	3 m
Load support (tensile force)	Rod end
Mounting - force application	Threaded hole M12
Mounting - force dissipation	Threaded hole M12

Construction

Functions	
Auto-off interval(s) in battery mode/rechargeable battery mode	1 - 60 min
Peak function	✓
Statistic function	✓
Limit-setting function	✓
Memory function	✓
Interfaces	RS-232 standard

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V
Input voltage device / power [Max]	12 V, 400 mA
Plug-in power supply type	Power adapter
Supplied power supply	Battery & Power supply
Plug-in power supply / adapter for countries - included with the delivery	UK
Rechargeable battery charging time	4 h
Rechargeable battery operating time - backlight on	10 h
Rechargeable battery operating time - backlight off	12 h
Battery / accumulator type	NiMH

Environmental conditions	
Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	325×185×165 mm
Net weight	1,556 kg
Shipping method	Parcel service
Net weight approx.	1,6 kg

1

KERN FH 5KUK



Universal digital force gauge for tensile and compressive force measurements with external load cell, with plug-in power supply for UK

Gross weight approx.	2,8 kg
Shipping weight	2,734 kg

Services (optional)	
Article number for DAkkS calibration (tensile force)	963-163
Article number for DAkkS calibration (compressive force)	963-263
Article number for DAkkS calibration (tensile force/compressive force)	963-363
Article number for factory calibration (tensile force)	961-163
Article number for factory calibration (compressive force)	961-263
Article number for factory calibration (tensile force/compressive force)	961-363

Pictograms

STANDARD





















OPTION







