KERN FH 100KUK



Universal digital force gauge for tensile and compressive force measurements with external load cell, with plug-in power supply for UK



Category	
Brand	Sauter
Product categoriy	Force measurement
Product group	Digital force gauge (external measuring cell)
Product family	FH-M

Measuring S	System
-------------	--------

U ,	
Default unit	kN
Tolerance (% of [Max])	0,5%
Measuring range force [Max] (N)	100 kN
Readability force [d] (N)	50 N
Directions of force	tension compression
Measuring head measuring frequency	2 kHz
Number of platforms / channels	1
Overload protection (% of [Max])	150%
Internal data memory: Number of value groups	1
Internal data memory: Number of individual values	10

Approval

CE mark

Display

Diopiay		
Display type	LCD	
Display digit height	10 mm	
Screen reversible	1	

1

Construction

Construction	
Dimension display device (W×D×H)	230×66×36 mm
Dimension housing (W×D×H)	230×66×36 mm
Dimensions completely mounted (W×D×H)	230×66×36 mm
Material display housing	Plastics
Cable length	3 m
Load support (tensile force)	Rod end
Mounting - force application	Threaded hole M30 × 2
Mounting - force dissipation	Threaded hole M30 × 2
Functions	
Auto-off interval(s) in battery	1 - 60 min
mode/rechargeable battery mode	
Peak function	
Statistic function	√
Limit-setting function	
Memory function	
Interfaces	RS-232 standard
Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V
Input voltage device / power [Max]	12 V, 400 mA
Plug-in power supply type	Power adapter
Supplied power supply	Battery & Power supply
Plug-in power supply / adapter for countries - included with the delivery	UK
Rechargeable battery charging time	4 h
Rechargeable battery operating time - backlight on	10 h
Rechargeable battery operating time - backlight off	12 h
Battery / accumulator type	NiMH
Environmental conditions	
Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C
Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	325×185×165 mm
Net weight	1,556 kg
Shipping method	Parcel service
Net weight approx.	1,6 kg

KERN FH 100KUK



Universal digital force gauge for tensile and compressive force measurements with external load cell, with plug-in power supply for UK

Gross weight approx.	2,8 kg
Shipping weight	2,734 kg
Services (optional)	
Article number for factory calibration (tensile force)	961-166
Article number for factory calibration (compressive force)	961-266
Article number for factory calibration (tensile force/ compressive force)	961-366

Pictograms

STANDARD





OPTION

