




## KL-0282-35 C

Counter-Hold Tool Kit (470mm long, adjustable)



### Product information

EN

⚠ Read and understand before use!

[www.gedore-automotive.com](http://www.gedore-automotive.com)



#### GEDORE Automotive GmbH

Breslauer Straße 41  
78166 - Donaueschingen  
Postfach 1329  
78154 Donaueschingen - GERMANY

☎ +49 (0) 771 / 8 32 23-0  
☎ +49 (0) 771 / 8 32 23-90  
✉ info.gam@gedore.com  
🌐 gedore-automotive.com

#### GEDORE TOOLS, INC.

Only for USA, Canada & Mexico / Sólo para EE.UU., Canadá y México  
Seulement pour les USA, le Canada et le Mexique  
7187 Bryhawke Circle, Suite 700  
North Charleston, SC 29418, USA

☎ +1-843 / 225 50 15  
☎ +1-843 / 225 50 20  
✉ info@gedoretools.com  
🌐 gedore.com

Version 1 - 02/2022

0282-35C\_EN220204.indd

## Product description

### KL-0282-35 C- Counter-hold tool kit (470mm long, adjustable)



Universal fit for perforated timing belt and timing chain sprockets, with or without camshaft adjustment. Installed, for example, in VW-Audi, Seat, Škoda, Alfa, BMW, Fiat, Lancia, Dacia, Mercedes, MG, Nissan, Ford, Opel, Porsche, Peugeot, Renault, Citroën, Rover, Volvo, Suzuki, Isuzu, Japanese vehicles, and many more.

**Alternative tools:** 3036, 0606-A1, 0606-A1Y, 0606-A2, 09917-68221, 1.860.831.000, 1.860.831.001, 1.860.831.002, 1.860.885.000, 1.870.815.000, 1.870.836.000, 15-030 A, 18G 1521, 205-072, 49 D011 102, 49 G011 103, 49 S120 710, 6016-T, 6310-T, EN-47634, EN-49979, KM-6245, KM-6347, MD998747, Mot.799, Mot.799-01, MP-1-216, T10172, T10172/1, T10172/2, T10172/4, T10172A, T10554, T20018, T20018A, T20018B, T20018B/1, T20018B/2, T20018B/3, T30004, T97T-6256-B

For professional counterholding of toothed belts and timing chain sprockets, with or without camshaft adjustment, which have at least two bores larger than 6.5mm diameter, or which are provided with M6 mounting threads. Required, for example, when loosening and tightening the fastening screws on the camshaft, balancer shaft, intermediate shaft, and injection pump shaft. Depending on the hole diameter and spacing, the counter-hold spanner can be individually adapted thanks to the large number of interchangeable bolts and knurled screws as well as the infinitely adjustable holder.

#### Recommended accessories:

- Locking tool kit VW 1.0 - **KL-0280-766 KA**,
- Locking tool kit VW 1.2 / 1.4 TSI / FSI - **KL-0280-767 KB**,
- Clamping key 30mm width - **KL-0284-171 A**



### Scope of supply / component overview

Item	Part no.	Description	Qty.
A	KL-0282-35	Counter-hold spanner, adjustable	1
B	KL-0282-311	Pin kit 18mm diameter	1
C	KL-0282-312	Pin kit 7.5mm diameter	1
D	KL-0282-313	Pin kit 6mm diameter	1
E	KL-0282-314	Knurled screw kit M6	1
-	KL-4990-2001	Plastic box	1

### Specifications

Pin diameter ..... 6 + 7.5 + 12 + 18mm  
 Knurled screw diameter: ..... M6 x 1.25mm  
 Length: ..... 470mm  
 Spanner width: ..... Variable from 14 - 130mm  
 For engine type: ..... Petrol + Diesel

## ⚠ Safety instructions and regulations

- ✔ **Before using** the special tool, read and understand **all** safety instructions and **follow** them for **safe use!**
- ✔ Use the special tool **as intended** and **always** carry out maintenance and repair work in compliance with the regulations on occupational safety and accident prevention as well as the vehicle manufacturer's instructions!
- ✔ **Before each use**, check the special tool **carefully** for damage, loose parts, or unauthorised modifications. **Never** use it if you notice any such deficiencies!
- ✔ **Always** wear your personal protective equipment (such as safety goggles, protective gloves, safety shoes) during work!