

Kraftform Kompakt VDE 62 iS PH/S Take it easy, # 2 x 157 mm



Kraftform Kompakt VDE



EAN:	4013288228598	Size:	157x12x12 mm
Part number:	05006517001	Weight:	29 g
Article number:	Kraftform Kompakt VDE 62 iS PH/S TiE	Country of origin:	CZ
		Customs tariff number:	82054000

- Kraftform Kompakt VDE interchangeable blade for PlusMinus screws slotted/Phillips
- Reduced shaft diameter and integrated insulation protection
- Insulated, individually tested as per IEC 60900
- 9 mm hex drive with with entry chamfer
- Black Point tip for enhanced corrosion protection and an exact fit
- Take it easy tool finder: Colour coding by profile and laser-engraved size indication
- Hexagonal anti-roll feature against rolling away

VDE blade for Kraftform Kompakt handle/interchangeable blade system. Combination profile slotted and Phillips, especially for use with magnetic rails, fuse boxes, switches, relays. Lightning-fast blade changes without special tools. Individually tested at 10,000 V for safe working at the approved voltage of 1,000 V. Reduced blade diameter with integrated protective insulation, low-lying screw and spring elements can be easily reached and operated. The Wera Black Point tip offers fitting accuracy and optimised corrosion protection. With "Take it easy" Tool finder: Colour coding by profile and laser-engraved size indication. The hexagonal anti-roll protection avoids blades from rolling away unintentionally.



Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_kompakt_vde_kraftform_kompakt_vde_62_is_ph_s_tie.html

Wera - Kraftform Kompakt VDE 62 iS PH/S TiE
05006517001 - 4013288228598

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Kompakt VDE

Individually tested



Testing the tool for dielectric strength at 10,000 volt gives the user the peace of mind that their tool has been tested for its most important property, insulation. Wera VDE tools are subjected to this test piece by piece which guarantees safe working at up to 1,000 volt.

Kraftform Kompakt VDE blades



The 157 mm length blades are suitable for Wera Kraftform bitholding screwdrivers 7400 VDE, 837 i RA, 827 T i and 817 VDE.

Handle/interchangeable blade system – Kraftform Kompakt VDE




The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

PlusMinus screwdrivers




For the use in terminal blocks, control cabinets, switches, relays, sockets etc.

VDE interchangeable blade with reduced shaft diameter




Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

“Take it easy”




The Kraftform Kompakt VDE blades are equipped with the “Take it easy” Tool finder. The colour coding by profile and the laser-engraved size indication make it easy to identify the required tool quickly.

Hexagonal anti-roll feature against rolling away



The Kraftform Kompakt blades come with an anti-roll protection. The hexagonal shape hinders the blade from rolling away annoyingly at the workplace.

Fast spinning



The palm of your hand is comfortably supported on the rounded shape of the rear end of the blades. This allows quick spinning of the blade and accelerates the screwdriving process.

Further versions in this product family:

			
		mm	inch
05006516001	# 1	157	6 3/16"
05006517001	# 2	157	6 3/16"

Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_kompakt_vde_kraftform_kompakt_vde_62_is_ph_s_tie.html

Wera - Kraftform Kompakt VDE 62 iS PH/S TiE
05006517001 - 4013288228598

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de