

9650 Magnetic rail Kraftform screwdriver set, 9 pieces

Kraftform Plus – Series 300



EAN: 4013288228970
Part number: 05051012001
Article number: 9650

Size: 410x150x55 mm
Weight: 1159 g
Country of origin: CZ
Customs tariff number: 82054000

- For every application the right tool
- The clips hold the tools perfectly
- With its strong magnet, the rail holds securely to metal surfaces. It can also be bolted to the wall.
- Multi-component Kraftform handle for high working speeds and ergonomic screwdriving
- VDE-insulated screwdrivers
- Lasertip tips for more secure fit in the screw head
- Chiseldriver for fastening, chiselling and loosening

Kraftform screwdriver set, 9-piece set, on a magnetic rail. Screwdriver all-round set. Kraftform Plus handle for comfortable ergonomic screwdriving, avoiding blisters and calluses. Hard handle zones for high working speeds, while soft handle zones guarantee a high torque transfer. 932 A with pound-thru hexagonal blade and impact cap; 350, 355 and 335 with Lasertip: The tips of Wera Lasertip screwdrivers are microscopically roughened with laser beams. This rough surface "bites" into the screw head and unintentional slipping is a thing of the past. 160 is VDE-insulated and with Lasertip. "Take it easy" Tool finder with colour coding by profile and size stamping - for quick and easy identification of the required tool. The clips hold the tools perfectly. With its strong magnet, the rail holds securely to metal surfaces. It can also be bolted to the wall.

Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_9650.html


Wera - 9650
05051012001 - 4013288228970




Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Plus – Series 300

Secure tool holding




With its strong magnet, the rail can be attached securely to metal surfaces.



The plastic magnetic rail offers space for up to 9 Kraftform screwdrivers. The clamping springs hold the tools securely.

Held by magnetic force



With its strong magnet, the rail can be attached securely to metal surfaces.

Screw mounting



The rail can also be bolted to the wall.

Series 900 – the Chiseldriver



The chiseldriver is the solution for jobs that require more than just screwdriving. For fastening, chiselling and loosening seized screws or hose clamps. With an integrated impact cap that extends service life and reduces the risk of splintering. With a pound-thru hexagon blade made from high-grade material for - zero-loss transfer of high forces when struck with a hammer. The tough viscous tempered material prevents the blade from splintering or breaking. More TORQUE can be transferred by attaching an open-jawed or ring spanner to the integrated hexagon bolster.

Kraftform Plus – Series 100 VDE




Our screwdrivers are tested for dielectric strength under a 10,000 volt load to make sure that their most important property, their insulation, has been exhaustively tested. Each individual Wera VDE screwdriver is subjected to this test to guarantee safe working up to 1,000 volts.

Kraftform Screwdrivers Series 300



Kraftform Plus screwdrivers - ergonomics you can grasp. They relieve the entire hand-arm system even when used intensively. Along with other technical and product advantages such as the Lasertip for a secure fit in the screw head, Kraftform screwdrivers are the ideal choice whenever manual screwdriving jobs are concerned.

Lasertip prevents slipping out



It happens time and time again that the tip slips out of the screw head when screwdriving, sometimes damaging valuable surfaces or even causing injury. The tips of the Wera Lasertip screwdrivers are microscopically roughened by means of a laser. This rough surface literally "bites" itself firmly into the screw head. Slipping out becomes a thing of the past.

Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_9650.html

Wera - 9650
05051012001 - 4013288228970

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de



9650 Magnetic rail Kraftform screwdriver set, 9 pieces

Kraftform Plus – Series 300





Set contents:



932 A Screwdriver for slotted screws, 1 x 5.5 x 100 mm

	05018264001	1x	1 x 5.5 x 100 mm
	05018266001	1x	1.2 x 7 x 125 mm



350 PH Screwdriver for Phillips screws, PH 2 x 100 mm

	05008720001	1x	PH 2 x 100 mm
			



355 PZ Screwdriver for Pozidriv screws, PZ 1 x 80 mm

	05009310001	1x	PZ 1 x 80 mm
	05009315001	1x	PZ 2 x 100 mm



367 Screwdriver for TORX® screws, TX 20 x 100 mm

	05028010001	1x	TX 20 x 100 mm
	05028012001	1x	TX 25 x 100 mm


335 Screwdriver for slotted screws, 0.8 x 4 x 100 mm

	05110004001	1x	0.8 x 4 x 100 mm
			

160 iS VDE Insulated screwdriver with reduced blade diameter for slotted screws, 0.6 x 3.5 x 100 mm

	05006440001	1x	0.6 x 3.5 x 100 mm
			

9611 Magnetic rail for up to 9 Kraftform screwdrivers, empty, 30 x 400 mm

	05136414001	1x	30 x 400 mm
---	-------------	----	-------------

Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_9650.html

Wera - 9650
05051012001 - 4013288228970

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de