




KL-0280-768 E

Vibration Damper Mounting Device VW-Audi



Product information EN
⚠ Read and understand before use!



www.gedore-automotive.com

GEDORE Automotive GmbH

Breslauer Straße 41
78166 - Donaueschingen
Postfach 1329
78154 Donaueschingen - GERMANY

☎ +49 (0) 771 / 8 32 23-0
☎ +49 (0) 771 / 8 32 23-90
✉ info.gam@gedore.com
🌐 gedore-automotive.com

GEDORE TOOLS, INC.

Only for USA, Canada & Mexico / Sólo para EE.UU., Canadá y México
Seulement pour les USA, le Canada et le Mexique
7187 Bryhawke Circle, Suite 700
North Charleston, SC 29418, USA

☎ +1-843 / 225 50 15
☎ +1-843 / 225 50 20
✉ info@gedoretools.com
🌐 gedore.com

Version 1 - 09/2021

Product description

KL-0280-768 E - Vibration damper mounting device VW-Audi

Suitable for VW, Audi, Seat und Škoda mit 1.8 + 2.0 TFSI / FSI direct-injection petrol engines.

Installed for example on VW Amarok (2H), Arteon (3H), Beetle (5C), CC (358), Eos (1F), Golf VI (5K), Golf VII (5G), Jetta (16, 1K), Passat (362, 365, 3C, 3G), Passat CC (35), Polo (6C), Scirocco (13), Sharan (7N), T5 (7E), T6 (SF), Tiguan (5N, AD, BW), Touran (5T), T-Roc (A1); Audi A1 (8X), A3 (8P, 8V), A4 (8K, 8W), A5 (8F, 8T, F5), A6 (4G), A7 (4G), Q3 (8U), Q5 (8R, FY), Q7 (4M), TT (8J, FV); Seat Alhambra (710/711), Altea (5P), Ateca (KH), Exeo (3R), Ibiza (6J, 6P), Leon (1P, 5F); Škoda Kodiaq (NS), Octavia (1Z, 5E), Superb (3T, 3V), Yeti (5L).

(Engine codes: BWA, BYT, BZB, CABA, CABD, CAEA, CAEB, CAED, CAWA, CAWB, CBFA, CCTA, CCTB, CCZA, CCZB, CCZC, CCZD, CDAA, CDAB, CDAB, CDHA, CDHB, CDNB, CDNC, CDND, CESA, CETA, CFKA, CFPA, CGYA, CHHA, CHHB, CHHC, CHJA, CJEB, CJEE, CJK, CJKB, CJSA, CJSB, CJSC, CJXA, CJXB, CJXC, CJXE, CJXF, CJXG, CJXH, CNCB, CNCD, CNCE, CNTA, CNTC, CPKA, CPLA, CPMA, CPMB, CPPA, CPRA, CPSA, CULA, CULB, CULC, CVKB, CWZA, CXDA, CYFB, CYGA, CYMC, CYNB, CYPA, CYPB, CYRB, CYRC, CZPA, CZPB, DAJA, DAJB, DAXB, DAXC, DAYB, DBPA, DDWA, DEDA, DEMA, DGUA, DGVA, DJHA, DJHC, DLBA)


Alternative tool: T10531

The mounting device allows the vibration damper to be held in the correct installation position, and the timing chain sprocket to be pressed against and fixed to the crankshaft when removing and installing the vibration damper and when changing the timing chain.

The timing chain sprocket on the crankshaft is held solely by the contact pressure of the central screw. For this reason, it must be fixed to the crankshaft before unscrewing the central screw to prevent the timing from being changed by turning.

Recommended Accessories:

KL-0280-763 K - Locking Tool Set VW 1.8 + 2.0 TFSI / TSI



Scope of delivery / Component overview

Pos.	Part no.	Description	Qty	Alternative tool	
1	KL-0280-7681	Fixing of vibration damper	1		
2	KL-0280-7683	Fixing mandrel 93.2mm	1	T10531/1	T10531
3	KL-0280-7682	Fixing mandrel 114.2mm	1		
4	KL-0280-7685	Crankshaft clamping device	1	T10531/2	
5	KL-0280-7684	Centring piece	1	T10531/3	
6	KL-0280-7686	Threaded bushing	1	T10531/4	
-	KL-0280-7689	Foam insert	1		
<p>i Storage system: Plastic case - KL-4990-9274</p>					

EN

Specifications

Weight: 1.5kg

⚠ Safety instructions and regulations

- ✔ **Before using** the tool, read and understand all safety instructions and **follow** them for **safe use!**
- ✔ Ensure that maintenance and repair work on motor vehicles is only carried out by trained specialists in specialist automotive workshops, taking into account occupational safety and accident prevention as well as the instructions of the vehicle manufacturer!
- ✔ **Prior to each use**, check the tool **carefully** for damage, loose parts or unauthorised modifications. **Never** use it if you notice any such deficiencies!
- ✔ Use the tool **as intended** and **always** observe the vehicle-specific application procedures in the vehicle manufacturer's repair manual!
- ✔ **Always** wear your personal protective equipment (*for example safety goggles, protective gloves, safety shoes*) when working!

GEDORE-Werkzeugfabrik GmbH & Co. KG

Remscheider Straße 149
42899 - Remscheid
Postfach 120361
47873 Remscheid
GERMANY

Vertrieb DEUTSCHLAND

☎ +49 (0) 2191 / 596-0
☎ +49 (0) 2191 / 596-230
✉ info@gedore.com
🌐 www.gedore.com

Sales INTERNATIONAL

☎ +49 (0) 2191 / 596-910
☎ +49 (0) 2191 / 596-911
✉ info@gedore.com
🌐 www.gedore.com

GEDORE TOOLS, INC.

Only for USA, Canada & Mexico
Sólo para EE.UU., Canadá y México
Seulement pour les USA, le Canada et le Mexique
7187 Bryhawke Circle, Suite 700, North Charleston, SC 29418, USA

☎ +1-843 / 225 50 15
☎ +1-843 / 225 50 20
✉ info@gedoretools.com
🌐 www.gedoretools.com

Worldwide GEDORE service centers and offices are listed on the Internet at: www.gedore.com

GEDORE Automotive GmbH

Breslauer Straße 41
78166 - Donaueschingen
Postfach 1329
78154 Donaueschingen
GERMANY

Vertrieb DEUTSCHLAND

☎ +49 (0) 771 / 8 32 23-0
☎ +49 (0) 771 / 8 32 23-90
✉ info.gam@gedore.com
🌐 gedore-automotive.com



www.gedore-automotive.com