

Flywheel-Rotating Tools



01/2020







KL-0363-2 A KL-0363-3 A KL-0363-4 KL-0363-5 KL-0363-7

KL-0363-8

KL-0363-9 A

(EN)

www.gedore-automotive.com

GEDORE Automotive GmbH

Breslauer Straße 41 78166 Donaueschingen Postfach 1329 DE-78166 Donaueschingen, Germany T+49 (0) 771 / 8 32 23-0 F+49 (0) 771 / 8 32 23-90 info.gam@gedore.com www.gedore-automotive.com


GEDORE WELTWEIT / GEDORE WORLDWIDE


Weltweite GEDORE Servicestellen / Niederlassungen finden Sie im Internet unter: www.gedore.com Worldwide GEDORE service centers / offices are listed on the Internet at: www.gedore.com

GEDORE TOOLS, INC.

Only for USA, Canada & Mexico Sólo para EE.UU., Canadá y México Seulement pour les USA, le Canada et le Mexique

7187 Bryhawke Circle, Suite 700 North Charleston, SC 29418, USA Phone +1-843 / 225 50 15 Fax +1-843 / 225 50 20 info@gedoretools.com















Flywheel-Rotating Tools

Field of Application

These tools allow the user to accurately rotate the engine for valve setting or other maintenance and service work.

Technical Data

Drive1/2"□

KL-0363-2 A Flywheel-Rotating Tool with 2 Gear Wheels

Applicable to:

Mercedes lorries equipped with either a 6-, 8- or 10-cylinder

MAN lorries equipped with a 12-cylinder engine.

Engine codes: Mercedes OM401, OM402, OM403, OM409, OM421, OM422, OM423, OM429, OM441, OM442, OM444, OM446, OM447, OM457, OM489, OM541, OM542; MAN D2842

KL-0363-3 A Flywheel-Rotating Tool with 3 Gear Wheels

Applicable to:

Mercedes lorries equipped with either a 4-, 6- or 8-cylinder

MAN lorries equipped with either a 5-, 6- or 8-cylinder engine. Engine codes: Mercedes OM457, OM541, OM542, OM902, OM904, OM906, OM924, OM926; MAN D25, D28

KL-0363-4 Flywheel-Rotating Tool with 1 Gear Wheel

Applicable to:

MAN lorries equipped with either a 6- or 8-cylinder engine. Engine codes: D20, D25, D26, D28

KL-0363-7 Flywheel-Rotating Tool, Scania

Applicable to:

Scania lorries equipped with either a 5-, 6- or 8-cylinder engine. Engine codes: DC 12, DC 13, DC 16

KL-0363-5 Flywheel-Rotating Tool, Volvo

Applicable to:

Volvo and Renault lorries equipped with a 6-cylinder engine. Engine codes: Volvo D9A, D11B, D12, D16C; Renault DXi11, DXi12

KL-0363-8 Flywheel-Rotating Tool, Volvo

Applicable to:

Volvo and Renault lorries equipped with a 6-cylinder engine. Engine codes: Volvo D13; Renault DXi13

KL-0363-9 A Flywheel-Rotating Tool, DAF

Applicable to:

DAF lorries equipped with a 6-cylinder (Euro 5 & 6) engine. Engines fitted to DAF XF 105 (Euro 5) for example.

Engine codes: MX300, MX340, MX375

Warnings and Notes

- Any work on vehicles/engines should only be performed by qualified specialist personnel observing and complying with the directions, provisions, and safety regulations specified by the vehicle manufacturer!
- Always refer to the vehicle manufacturer's data and instructions as only these apply to all work that is carried out on the vehicle.

