

## KL-0115-200 /-210

Wheel Hub Grinder, Car, Commercial Vehicle



### GEDORE Automotive GmbH

Breslauer Straße 41  
78166 - Donaueschingen  
Postfach 1329  
78154 Donaueschingen - GERMANY  
☎ +49 (0) 771 / 8 32 23-0  
☎ +49 (0) 771 / 8 32 23-90  
✉ info.gam@gedore.com  
🌐 www.gedore-automotive.com



[www.gedore-automotive.com](http://www.gedore-automotive.com)



12/2023

KL-0115-200\_210 (EN231124).indd

## PRODUCT DESCRIPTION

### KL-0115-2.. - Wheel hub grinder for stud bolts

For universal use on wheel hubs with wheel studs.


For quick cleaning of the rim contact surface, especially on wheel hubs with wheel studs.

Solid corrosion residues can be removed simply and easily in a single operation by placing directly over the wheel studs.

The patented 8-sided quick-change holder ensures precise centring between the base body and the grinding disc.

### KL-0115-200 - Wheel hub grinder for stud bolts, cars and vans

For cars and vans



### Specifications

Drive (square):..... 1/2"

Outer dia. .... 50mm

Outer dia. (2):..... 40mm

Length: ..... 110mm


Weight: ..... 500g

### Scope of delivery

Item	Description	Qty.
A	Base unit	1
B	Grinding wheel set	1
B1	Grinding wheel large	6
B2	Grinding wheel small	5

**KL-0115-210 - Wheel hub grinder for stud bolts, commercial vehicles and vans**

For commercial vehicles and vans



**Specifications**

Drive (hexagon): ..... 3/8"  
 Outer dia. .... 57mm  
 Length: ..... 170mm  
 Weight: ..... 900g

**Scope of delivery**

Item	Description	Qty.
A	Base unit	1
B	Grinding wheel set	1
B1	Grinding wheel large	6
B2	Grinding wheel small	5

**⚠ SAFETY INSTRUCTIONS AND REGULATIONS**

- Read and understand this product information **before using** the special tool. This serves to familiarise you with the special tool for **safe use!**
- Use the special tool **as intended** and **always** carry out maintenance and repair work in compliance with the regulations on occupational safety and accident prevention as well as the vehicle manufacturer's instructions!
- Before each use**, check the special tool **carefully** for damage, loose parts, or unauthorised modifications. **Never** use it, if you notice any such deficiencies!
- Always** wear your personal protective equipment, e.g. safety goggles, protective gloves, safety shoes, during work if necessary!
- Interrupt your work **immediately** if you are unsure about using the special tool, and contact **GEDORE Automotive GmbH** if necessary!
- Dispose of the special tool and its packaging material in an environmentally compatible way in accordance with the legal requirements. If necessary, ask your local authorities or **GEDORE Automotive GmbH** about environmentally friendly disposal options!

## GEDORE Automotive GmbH

Breslauer Str. 41  
78166 Donaueschingen  
GERMANY  
Tel: +49 771 83 223 0  
Fax: +49 771 83 223 90  
[www.gedore-automotive.com](http://www.gedore-automotive.com)

## GEDORE International:

### GEDORE Torque Solutions GmbH

Bertha-Benz-Straße 12  
71665 Vaihingen/Enz  
GERMANY  
Tel: +49 70 42 94 41 0  
Fax: +49 70 42 9441 41  
[www.gedore-torque-solutions.com](http://www.gedore-torque-solutions.com)

### GEDORE France SARL

Parc d'activités des Béthunes – La Mare II 10, avenue du Fief – Bâtiment 12  
BP 79144 - Saint-Ouen-L'Aumône / 95074 CERGY PONTOISE CEDEX  
FRANCE  
Tél: +33 1 34 40 16 60  
Fax: +33 1 34 40 16 61  
[www.gedore.fr](http://www.gedore.fr)

### GEDORE Polska Sp. z.o.o.

Żwirki i Wigury 56, Mikołów  
POLAND  
Tel: +48 32 738 40-10  
Fax: +48 32 738 40-20  
[www.gedore.pl](http://www.gedore.pl)

### GEDORE India Pvt. Ltd.

Plot No. 148, Sector-3, IMT Manesar  
Gurugram, Haryana-122051  
INDIA  
Tel: +91 124 4087979  
[sales@gedoreindia.com](mailto:sales@gedoreindia.com)  
[www.gedore.in](http://www.gedore.in)

### GEDORE Tools South Africa (PTY) Ltd.

103 Qashana Khuzwayo Road, Durban / Kwazulu-Natal  
New Germany, 3610  
SOUTH AFRICA  
Tel: +27 3 17 05 35 87  
Fax: +27 3 17 05 47 35  
[www.gedore.co.za](http://www.gedore.co.za)

### GEDORE Tool Trading Co., Ltd. Shanghai, China

1/F, Block 2, 1358 Pingan Road  
Minhang, Shanghai, China 201109  
CHINA  
Tel: +86 21 33 88 72-58  
Fax: +86 21 33 88 72-59  
[www.gedore.cn](http://www.gedore.cn)

### GEDORE Ibèrica S.L., Spain

c/Arangutxi 12, Poligono Industrial de Júndiz  
01015 Vitoria Alava  
SPAIN  
Tel: +34 945 292 262  
Fax: +34 945 292 199  
[www.gedore.es](http://www.gedore.es)

## GEDORE Headquarter:

### GEDORE Werkzeugfabrik GmbH & Co. KG

Remscheider Str. 149  
42899 Remscheid  
GERMANY  
Tel: +49 2191 596 900  
Fax: +49 2191 596 999  
[www.gedore.com](http://www.gedore.com)

### GEDORE AUSTRIA GmbH

Gedore-Straße 1  
8190 Birkfeld  
AUSTRIA  
Tel: +43 3174 3636 0  
Fax: +43 31 74 36 38 320  
[www.gedore.at](http://www.gedore.at)

### GEDORE Torque UK Ltd.

Tannery Ln, Gosden Common  
Guildford GU5 0AJ  
UK  
Tel: +44 14 83 89 27 72  
Fax: +44 14 83 89 85 36  
[www.gedore-torque.com](http://www.gedore-torque.com)

### GEDORE Technag BV, Netherlands

Flemingweg 7  
2408 AV Alphen aan Den Rijn  
NETHERLANDS  
Tel: +31 1 72 42 73 50  
Fax: +31 1 72 42 73 60  
[www.gedore.nl](http://www.gedore.nl)

### Ferramentas GEDORE do Brasil S.A.

Rua Vicentina Maria Fidélis, 275 Bairro Vicentina  
São Leopoldo - RS - CEP: 93025-340  
BRASIL  
Tel: +51 35 89 92 00  
Fax: +51 35 89 92 22  
[www.gedore.com.br](http://www.gedore.com.br)

### GEDORE UK Ltd.

Marston St, Skipton  
North Yorkshire BD23 1TF  
UNITED KINGDOM  
Tel: +44 17 56 70 67 00  
Fax: +44 17 56 79 80 83  
[www.gedoreuk.com](http://www.gedoreuk.com)

### GEDORE Torque Ltd., UK

Bramley  
Guildford, Surrey, GU5 0AJ  
UNITED KINGDOM  
Tel: +44 1483 894476  
[www.gedore-torque.com](http://www.gedore-torque.com)

### GEDORE Tools Inc. USA

4055 Faber PI Dr  
North Charleston, SC 29405  
USA  
Tel: +1 843 225 5015  
[www.gedoretools.com](http://www.gedoretools.com)