


## 840/0 Hex-Plus Micro bits for hexagonal socket head screws, 1.3 x 30 mm

Bits for hexagonal socket screws



|                        |               |                               |           |
|------------------------|---------------|-------------------------------|-----------|
| <b>EAN:</b>            | 4013288234544 | <b>Size:</b>                  | 30x5x4 mm |
| <b>Part number:</b>    | 05058109001   | <b>Weight:</b>                | 5 g       |
| <b>Article number:</b> | 840 Micro     | <b>Country of origin:</b>     | CZ        |
|                        |               | <b>Customs tariff number:</b> | 82079030  |

- For hexagonal socket head screws
- With Hex-Plus profile (prevents rounding-out of hexagonal socket screws)
- Tough for hard materials
- 4 mm hexagonal drive

Bits for hexagonal socket screws. Hex-Plus offers larger contact surfaces in the screw head. The notch effect is reduced to a minimum and the destruction of the screw head is almost eliminated. Tough, for universal use. 4 mm hexagonal.

### Web link

[https://products.wera.de/en/new\\_products\\_2025\\_bits\\_for\\_hexagonal\\_socket\\_screws\\_840\\_micro.html](https://products.wera.de/en/new_products_2025_bits_for_hexagonal_socket_screws_840_micro.html)

Wera - 840 Micro  
05058109001 - 4013288234544

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

Bits for hexagonal socket screws

Tough bits



Tough Wera bits prevent the tip from breaking prematurely. Z-bits usually are the bit for universal screwdriving applications.

Further versions in this product family:

|                    |  |  |  |  |
|--------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                    | mm                                                                                | mm                                                                                | inch                                                                                | mm                                                                                  |
| 05058108001        | 0.9                                                                               | 30                                                                                | 1 3/16"                                                                             | 2.0                                                                                 |
| <b>05058109001</b> | <b>1.3</b>                                                                        | <b>30</b>                                                                         | <b>1 3/16"</b>                                                                      | <b>2.6</b>                                                                          |
| 05058110001        | 1.5                                                                               | 30                                                                                | 1 3/16"                                                                             | 2.6                                                                                 |
| 05058111001        | 2.0                                                                               | 30                                                                                | 1 3/16"                                                                             | 2.6                                                                                 |
| 05058112001        | 2.5                                                                               | 30                                                                                | 1 3/16"                                                                             | 2.6                                                                                 |

Web link

[https://products.wera.de/en/new\\_products\\_2025\\_bits\\_for\\_hexagonal\\_socket\\_screws\\_840\\_micro.html](https://products.wera.de/en/new_products_2025_bits_for_hexagonal_socket_screws_840_micro.html)

Wera - 840 Micro  
05058109001 - 4013288234544

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)