

Kraftform Kompakt VDE 15 Torque 1.2-3.0 Nm extra slim 1 Tool finder, 15 pieces

Series 7400 Insulated Kraftform Torque Screwdrivers



EAN:	4013288229915	Size:	230x130x65 mm
Part number:	05006605001	Weight:	748 g
Article number:	Kraftform Kompakt VDE 15 Torque 1,2-3,0 Nm extra slim 1 Tool Finder	Country of origin:	CZ
		Customs tariff number:	82054000

- Kraftform Kompakt VDE torque screwdriver set with adjustable torque
- Adjustable Kraftform VDE torque holder exclusively for Wera VDE interchangeable blades
- VDE blades (157 mm length) with practical spinning function, anti-roll protection and "Take it easy" Tool finder: Colour coding by profile and laser-engraved size indication
- Individually tested tools as per IEC 60900
- In robust pouch
- Suitable for Wera 2go

15-piece torque VDE blade set. One torque VDE bitholding screwdriver with adjustable torque value from 1.2-3.0 Nm. With ergonomic Kraftform Plus handle, with hard handle zones ensuring high working speeds while soft handle zones guarantee a high torque transfer. Includes 14 blades (12 of which with reduced blade diameter) with integrated protective insulation. With "Take it easy" Tool finder: Colour coding by profile and laser-engraved size indication - for quick and easy identification of the required tool. In a robust belt pouch. The textile box features a fleece zone at the back. Using the provided self-adhesive hook and loop fastener strips, the textile box can be attached to the Wera 2go components. Or to the wall, shelf or workshop trolley.



Web link

https://products.wera.de/en/torque_tools_insulated_torque_tools_series_7400_insulated_kraftform_torque_screwdrivers_kraftform_kompakt_vde_15_torque_1_2-3_0_nm_extra

Wera - Kraftform Kompakt VDE 15 Torque 1,2-3,0 Nm extra slim 1 Tool Finder
05006605001 - 4013288229915

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de


Series 7400 Insulated Kraftform Torque Screwdrivers

Individually tested



Each Kraftform Kompakt VDE set has been tested individually at 10,000 volts, in accordance with IEC 60900. This ten-times-higher testing load guarantees safe working at their maximum permitted load of 1,000 volts.

Handle/interchangeable blade system – Kraftform Kompakt VDE




The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

Kraftform adjustable torque handle for Electricians




Easy-to-read scale value. Measurement accuracy is $\pm 6\%$ in accordance with the standard EN ISO 6789.

“Take it easy”



The Kraftform Kompakt VDE blades are equipped with the “Take it easy” Tool finder. The colour coding by profile and the laser-engraved size indication make it easy to identify the required tool quickly.

VDE interchangeable blade with reduced shaft diameter




Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

PlusMinus screwdrivers




For the use in terminal blocks, control cabinets, switches, relays, sockets etc.

Kraftform adjustable torque handle for Electricians



Simple setting of the required torque by hand.

Excess-load signal



Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.

Web link

https://products.wera.de/en/torque_tools_insulated_torque_tools_series_7400_insulated_kraftform_torque_screwdrivers_kraftform_kompakt_vde_15_torque_1_2-3_0_nm_extra

Wera - Kraftform Kompakt VDE 15 Torque 1,2-3,0 Nm extra slim 1 Tool Finder
05006605001 - 4013288229915

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Kompakt VDE 15 Torque 1.2-3.0 Nm extra slim 1 Tool finder, 15 pieces



Series 7400 Insulated Kraftform Torque Screwdrivers


Set contents:


Series 7400 VDE Kraftform adjustable torque handle (0.3-3.5 Nm), 7441 VDE x 1.2-3.0 Nm

 05074750001 1x 7441 VDE x 1.2-3.0 Nm




Kraftform Kompakt VDE 62 iS Take it easy, PH 1 x 157 mm


 05006512001 1x PH 1 x 157 mm

 05006513001 1x PH 2 x 157 mm




Kraftform Kompakt VDE 65 iS Take it easy, PZ 1 x 157 mm


 05006526001 1x PZ 1 x 157 mm

 05006527001 1x PZ 2 x 157 mm




Kraftform Kompakt VDE 65 iS PZ/S Take it easy, # 1 x 157 mm

 05006530001 1x # 1 x 157 mm

 05006531001 1x # 2 x 157 mm





Kraftform Kompakt VDE 67 i TORX® Take it easy, TX 10 x 157 mm


 05006534001 1x TX 10 x 157 mm




Kraftform Kompakt VDE 67 iS TORX® Take it easy, TX 15 x 157 mm

 05006540001 1x TX 15 x 157 mm

 05006541001 1x TX 20 x 157 mm

 05006542001 1x TX 25 x 157 mm





Kraftform Kompakt VDE 60 i Take it easy, 0.4 x 2.5 x 157 mm


 05006500001 1x 0.4 x 2.5 x 157 mm



Kraftform Kompakt VDE 60 iS Take it easy, 0.6 x 3.5 x 157 mm

 05006506001 1x 0.6 x 3.5 x 157 mm


 05006507001 1x 0.8 x 4 x 157 mm

 05006508001 1x 1 x 5.5 x 157 mm



Hook and Loop Fastener Strip 70, 50 x 70 mm

1x 50 x 70 mm



Web link

https://products.wera.de/en/torque_tools_insulated_torque_tools_series_7400_insulated_kraftform_torque_screwdrivers_kraftform_kompakt_vde_15_torque_1_2-3_0_nm_extra

Wera - Kraftform Kompakt VDE 15 Torque 1,2-3,0 Nm extra slim 1 Tool Finder
05006605001 - 4013288229915

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de