

KERN PCJ 6000-1M-Prepack

KERN

The complete solution for prepack processes, with optional verification



Software EasyTouch

**SET-17
PrePack**

Category

Brand	KERN
Product category	Balance software bundle
Product group	Prepack balance
Product family	PCJ-Prepack

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	6 kg
Readability [d]	100 mg
Reproducibility	100 mg
Linearity	± 300 mg
USP Minimum weight of sample (k = 2, U = 0.1%)	200 g
Minimum weight [Min]	5 g
Resolution	60.000
Tare range	6 kg
Possible calibration points	2 kg; 6 kg
Automatic adjustment - Standard temperature deviation	2 °C
Automatic adjustment - Standard time interval	8 h
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	300 mg
Conformity assessment possible	✓

Construction

Dimension housing (W×D×H)	163×245×80 mm
Dimensions completely mounted (W×D×H)	163×245×80 mm
Dimensions weighing surface (W×D)	150×170 mm
Dimensions weighing surface	150×170 mm
Level indicator	✓
Levelling feet adjustable	✓

Functions

Alibi memory	internal memory
Alibi memory - number of memory spaces	250.000
Counting resolution (laboratory conditions)	30.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	200 mg
Smallest piece weight when piece counting - normal conditions	2 g

Interface

EasyTouch (ET) - Compatibility	Vollständig
--------------------------------	-------------

Power Supply

Battery operating time	20 h
Battery capacity	220 mAh
Battery voltage	3 V
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	48 h
Rechargeable battery charging time	8 h

Environmental conditions

Ambient temperature [Min]	15 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %

Approval

CE mark	✓
Conformity assessment possible ex works	✓
Verification scale interval [e]	1 g

Services (optional)

Article number for conformity assessment	965-217
Article number for DAkKS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Packing & Shipping

Delivery time	1 d
---------------	-----

KERN PCJ 6000-1M-Prepack



The complete solution for prepack processes, with optional verification

Dimensions packaging (W×D×H) 235×365×175 mm

Shipping method Parcel service


Net weight approx. 2,8 kg

Gross weight approx. 3,4 kg

Shipping weight 3,38 kg

Pictograms

STANDARD



OPTION



FACTORY

