

Garant
Socket set 1/2 inch, Number of tools: 32

Order data

Order number	953857 32
GTIN	4062406097257
Item class	91A

Description
Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

Rigid foam inlay, empty No. 952001 size 953857: 1 pc.

GARANT reversible ratchet, No. 640025 size 1/2: 1 pc.

GARANT extension No. 641029 size 75; 125; 250: 1 pc. each

GARANT T-handle No. 641329 size 295: 1 pc.

GARANT universal joint No. 641629 size 1/2: 1 pc.

GARANT hexagon socket No. 642229 size 8; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 24; 27; 30; 32; 34: 1 pc. each

GARANT hexagon screwdriver bit No. 643229 size 4; 5; 6; 7; 8; 10; 12; 14: 1 pc. each

Technical description

Width	250 mm
Width in G	10
Weight	4.26 kg
Number of tools	32
Depth in G	24

Depth	600 mm
Version	with socket
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	10×24
Square drive	1/2 in
Smallest suitable drawer front height	100 mm
Type of product	Rigid foam inlay

Accessories

T-handle, 1/2 inch overall length 295 mm	641329 295
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 7 mm	643229 7
Hexagon socket, 1/2 inch Width across flats 32 mm	642229 32
Reversible ratchet, 1/2 inch with ejector Type 1/2	640025 1/2
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 4 mm	643229 4
Hexagon socket, 1/2 inch Width across flats 21 mm	642229 21
Extension, 1/2 inch overall length 130 mm	641029 130
Extension, 1/2 inch overall length 255 mm	641029 255
Hexagon socket, 1/2 inch Width across flats 24 mm	642229 24
Rigid foam inlay for tool sets suitable for rigid foam set 953857	952001 953857
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 8 mm	643229 8
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 5 mm	643229 5
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 10 mm	643229 10
Hexagon socket, 1/2 inch Width across flats 17 mm	642229 17
Hexagon socket, 1/2 inch Width across flats 22 mm	642229 22

Hexagon socket, 1/2 inch Width across flats 16 mm	642229 16
Hexagon socket, 1/2 inch Width across flats 19 mm	642229 19
Hexagon socket, 1/2 inch Width across flats 10 mm	642229 10
Hexagon socket, 1/2 inch Width across flats 13 mm	642229 13
Hexagon socket, 1/2 inch Width across flats 30 mm	642229 30
Hexagon socket, 1/2 inch Width across flats 11 mm	642229 11
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 6 mm	643229 6
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 14 mm	643229 14
Hexagon socket, 1/2 inch Width across flats 34 mm	642229 34
Hexagon socket, 1/2 inch Width across flats 27 mm	642229 27
Hexagon socket, 1/2 inch Width across flats 8 mm	642229 8
Extension, 1/2 inch overall length 75 mm	641029 75
Hexagon socket, 1/2 inch Width across flats 18 mm	642229 18
Hexagon socket, 1/2 inch Width across flats 12 mm	642229 12
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 12 mm	643229 12
Hexagon socket, 1/2 inch Width across flats 15 mm	642229 15
Hexagon socket, 1/2 inch Width across flats 14 mm	642229 14
Universal joint, 1/2 inch Type 1/2	641629 1/2