



Socket set 3/8 inch square drive 29 pieces, Type: S



Order data

Order number	634120 S
GTIN	4013288173928
Item class	63F

Description

Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120.**

Application:

For hexagon head screws / nuts with thread M5 – M12 and for hexagon socket head screws with thread M4 – M10.

For Phillips and Pozidriv screws with thread M2 – M6 and for internal Torx® screws with thread M3.5 – M8.

Material:

Chrome molybdenum steel, matt chrome-plated.

Content:

With reversible ratchet No. 635295.

Supplied with:

Socket single hexagon: 9 pcs.

size 8; 10; 12; 13; 15; 16; 17; 18; 19 mm

Hexagon bit: 5 pcs. No. 675240 size 3; 4; 5; 6; 8

BITS for Phillips: 3 pcs. No. 675310 size 1/25; 2/25; 3/25

Pozidriv bit: 2 pcs. No. 675320 size 1/25; 2/25

BITS for Torx®: 6 pcs. No. 675340 size TX15; TX20; TX25; TX27; TX30; TX40

Extension with quick rotation sleeve: 1 pc. 200 mm

Wobbel extension: 1 pc. 76 mm

Adapter with quick-release holder: 1 pc. 3/8 inch square – 1/4 inch hexagon bit holder

Ratchet (size P): 1 pc. No. 635290 with push-through square

Ratchet (size S): 1 pc. No. 635295 with reversible ratchet

Presented in: Textile wallet with hook and loop fastener

Technical description

Number of pieces	29
Drive profile	Hexagon socket
Drive profile	Screwdriver for TORX® screws
Drive profile	Pozidriv screwdriver
Drive profile	Hexagon socket
Drive profile	Screwdriver for Phillips
Square drive	3/8 in
Width across flats	metric
Width across flats range, hexagon sockets	8-19 mm
Width across flats range, hexagon wrenches	3-8 mm
Manufacturer's designation	8100 SB 8
Packaging	Textile folding wallet, hook and loop fastening
Length	262 mm
Width	120 mm
Height	57 mm
Type of product	Socket spanner

Accessories

Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX27	675340 TX27
Bit for Phillips, 1/4 inch C 6.3 Cross-head size / overall length 1/25 mm	675310 1/25
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX25	675340 TX25
	675320 1/25

Bit for Pozidriv, 1/4 inch C 6.3 Cross-head size / overall length 1/25 mm

Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 6 mm

675240 6

Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 5 mm

675240 5

Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 3 mm

675240 3

Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX15

675340 TX15

Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 4 mm

675240 4

Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 8 mm

675240 8

Bit for Phillips, 1/4 inch C 6.3 Cross-head size / overall length 3/25 mm

675310 3/25

Bit for Pozidriv, 1/4 inch C 6.3 Cross-head size / overall length 2/25 mm

675320 2/25

Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX30

675340 TX30

Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX40

675340 TX40

Bit for Phillips, 1/4 inch C 6.3 Cross-head size / overall length 2/25 mm

675310 2/25

Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX20

675340 TX20

Precision ratchet "Zyklop Metal" reversible, 3/8 inch with ejector

635295