



Socket set 3/8 inch square drive 29 pieces, Type: P



Order data

Order number	634120 P
GTIN	4013288173867
Item class	63F

Description

Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120.**

Application:

For hexagon head screws / nuts with thread M5 – M12 and for hexagon socket head screws with thread M4 – M10.

For Phillips and Pozidriv screws with thread M2 – M6 and for internal Torx® screws with thread M3.5 – M8.

Material:

Chrome molybdenum steel, matt chrome-plated.

Content:

With push-through square No. 635290.

Supplied with:

Socket single hexagon: 9 pcs.

size 8; 10; 12; 13; 15; 16; 17; 18; 19 mm

Hexagon bit: 5 pcs. No. 675240 size 3; 4; 5; 6; 8

BITS for Phillips: 3 pcs. No. 675310 size 1/25; 2/25; 3/25

Pozidriv bit: 2 pcs. No. 675320 size 1/25; 2/25

BITS for Torx®: 6 pcs. No. 675340 size TX15; TX20; TX25; TX27; TX30; TX40

Extension with quick rotation sleeve: 1 pc. 200 mm

Wobbel extension: 1 pc. 76 mm

Adapter with quick-release holder: 1 pc. 3/8 inch square – 1/4 inch hexagon bit holder

Ratchet (size P): 1 pc. No. 635290 with push-through square

Ratchet (size S): 1 pc. No. 635295 with reversible ratchet

Presented in: Textile wallet with hook and loop fastener

Technical description

Drive profile	Hexagon socket
Drive profile	Hexagon socket
Drive profile	Pozidriv screwdriver
Drive profile	Screwdriver for Phillips
Drive profile	Screwdriver for TORX® screws
Square drive	3/8 in
Number of pieces	29
Width across flats	metric
Width across flats range, hexagon sockets	8-19 mm
Width across flats range, hexagon wrenches	3-8 mm
Manufacturer's designation	8100 SB 7
Packaging	Textile folding wallet, hook and loop fastening
Length	262 mm
Width	120 mm
Height	57 mm
Type of product	Socket spanner

Accessories

Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 5 mm	675240 5
Bit for Phillips, 1/4 inch C 6.3 Cross-head size / overall length 2/25 mm	675310 2/25
Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 6 mm	675240 6

Precision ratchet "Zyklop Metal" push-through square drive, 3/8 inch with ejector	635290
Bit for Pozidriv, 1/4 inch C 6.3 Cross-head size / overall length 2/25 mm	675320 2/25
Bit for Phillips, 1/4 inch C 6.3 Cross-head size / overall length 1/25 mm	675310 1/25
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX20	675340 TX20
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX25	675340 TX25
Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 3 mm	675240 3
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX15	675340 TX15
Bit for Pozidriv, 1/4 inch C 6.3 Cross-head size / overall length 1/25 mm	675320 1/25
Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 4 mm	675240 4
Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 8 mm	675240 8
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX40	675340 TX40
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX27	675340 TX27
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX30	675340 TX30
Bit for Phillips, 1/4 inch C 6.3 Cross-head size / overall length 3/25 mm	675310 3/25