



## Tool case "BIG twin" electrical, 63 pieces, Number of tools: 63



### Order data

Order number	680101 63
GTIN	4003773084228
Item class	73F

### Description

#### Version:

Comprehensive electrician's tool kit in a high quality tool case, opening both sides.

#### Content:

Electrician's spirit level: 1 pc. No. 467415 size 430  
 Pocket spirit level electric: 1 pc. No. 467484 size 70  
 "JOKER" double-ended ring spanner: 1 each size 10x13 mm  
 TwinKey® multi-function key: 1 pc. No. 623550  
 Socket set 1/4 inch, 28 pieces: 1 pc. No. 630295 size S  
 Posidriv screwdriver, insulated to VDE: 1 pc. size 1  
 Slot-head screwdriver, insulated to VDE: 1 pc. size 3.5 mm  
 Kraftform Kompakt VDE set, 16-piece: 1 pc. similar to No. 667260  
 Pointed combination pliers, chrome-plated, insulated to VDE: 1 pc. No. 701655 size 145  
 Water pump pliers Cobra® chemically blacked: 1 pc. No. 705800 size 180  
 Snipe nose pliers, angled, insulated to VDE: 1 pc. No. 713700 size 200  
 Heavy-duty side cutter, chrome-plated, insulated to VDE: 1 pc. No. 723500 size 200  
 Side cutters, chrome-plated, insulated to VDE: 1 pc. No. 725300 size 160  
 Universal stripping tool ErgoStrip®: 1 pc. No. 728091 size 8-13  
 Wire stripper, up to 10 mm<sup>2</sup>: 1 pc. No. 728630 size 10  
 Installation pliers, insulated to VDE: 1 pc. No. 728787 size 200  
 Crimping tool for terminal sleeves up to 16 mm<sup>2</sup>: 1 pc.

Electrician's chisels: 1 pc. No. 743000 size 250  
 Engineer's hammer: 1 each size 300 g  
 Pliers wrench: 1 pc. No. 813700 size 180  
 Fixed blade cable knife, insulated to VDE: 1 pc. No. 844410

**Note:**

**Supplied completely mounted in a tool case.**

**Technical description****Accessories**

Cable knife fixed fully insulated to VDE	844410
ErgoStrip® universal stripping tool for cable Ø 8-13 mm	728091 8-13
Pliers wrench overall length 180 mm	813700 180
Installation pliers VDE insulated overall length 200 mm	728787 200
Diagonal side cutter, chrome-plated VDE insulated overall length 200 mm	723500 200
Electrician's chisel overall length 250 mm	743000 250
Electrician's spirit level Length 430 mm	467415 430
Snipe-nose combination pliers, chrome-plated VDE insulated overall length 145 mm	701655 145
Snipe nose pliers, angled VDE insulated overall length 200 mm	713700 200
Socket set 1/4 inch square drive 28 pieces Type S	630295 S
Pocket spirit level Electric Length 70 mm	467484 70
TwinKey® multi-function key	623550
Water pump pliers Cobra® chemically blacked overall length 180 mm	705800 180
Wire stripping tool for conductor cross-section 10 mm <sup>2</sup>	728630 10
Diagonal side cutter, chrome-plated VDE insulated overall length 160 mm	725300 160