

Garant**Tool24 Smartline – upright cabinet fitted with tool sockets, for tool shanks: HSK50****Order data**

Order number	979101 HSK50
GTIN	4062406134051
Item class	9SA

Description**Version:**

The pull-out shelves are supported from the base and equipped with central locking (can be used for emergency release). The end faces of the hot-dip galvanised frames of the pull-out shelves have holes at intervals of 37 mm for mounting tool stands, carrying rails, storage shelf trays, and perforated tool boards. The pull-out frames are equipped with an anti-tilt device. The pull-out frames open automatically. This ensures quick access to the tools.

- **Storage of pre-set tools.**
- **Only for use in conjunction with a Tool24 Smartline Master Unit system.**
- **Available with 14 different configurations (for different tool shanks SK, VDI, C, HSK).**
- **Supplied with 24 carrier rails.**
- **Mountings suitable for tool stands, support rails, shelf trays and perforated tool panels.**
- **Distributed safe working load per pull-out frame: 600 kg.**
- **Maximum upright cabinet load: 2400 kg.**
- **Locking system for emergency release.**

Application:

Automatic industrial vending solution for storage and management of tools and C-items.

Colour:

Body RAL 7035 light grey, pull-out frames RAL 7016 anthracite **powder-coated.**

Note:

Upright cabinets place increased demands on the floor, since the pull-out frames run directly on the floor! The following pre-requirements for the installation site must be satisfied absolutely by the customer:

- **Flatness tolerance for finished floors as per DIN 18202.**
- **Angularity of a maximum of 2 millimetres over the measurement length of 1 metre.**
- **The subsurface must have a sufficient load-bearing capacity.**
- **Only place on ground that is absolutely level.**

The systems are prepared for wall or floor-mounting and must be secured against tilting. These upright cabinets can only be used in conjunction with a Tool24 Smartline Master Unit system No. 979001 S11M or No. 979001 S11M-EN, Tool24 PickOne Master Unit system No. 979201 DE or No. 979211 EN, and Tool24 Locker Master Unit system No. 979300 DE or No. 979310 EN.

Technical description

Number of tool carriers No. 970130	24
Number of tool sockets	336
Pull-out frame drawers width	155 mm
Depth	750 mm
Width	717 mm
Weight	320 kg
Axial spacing A	76 mm
Number of pull-out frames	4
Vertical pull-out frame usable height	1750 mm
Height	2000 mm
Vertical pull-out frame load capacity	600 kg
Series	Tool24 Smartline
Cabinet housing internal load capacity	2400 kg
Drawer runner extension	Anti-tilt lock
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Tool issuing system

Accessories

Tool carrier with tool sockets for tool shanks HSK50

970130 HSK50