

**Cordless angle grinder 18V, for 125 mm discs Ø, X-LOCK system****Order data**

Order number	077010 18V-10SC
GTIN	3165140974035
Item class	03C

Description**Version:**

- **Easy and quick:** Easy change of angle grinder accessories without parts that could be lost or need for additional tools.
- **Additional wrench no longer required.**
- **Comprehensive:** Huge range of angle grinders and accessories with complete backwards compatibility.
- **Maximum convenience** thanks to completely tool-less and quick accessory replacement.
- **Reliable:** Directional accessories can no longer be mounted incorrectly thanks to the innovative X-LOCK system. Maximum user protection thanks to acoustic signal upon correct mounting.
- **Clean working without annoying scratches!** Less prominent and fewer scuffs with X-Lock angle grinders.

125-mm **cordless angle grinder** from the new X-Lock system.

Supplied with:

Supplied with 2 pcs. ProCORE18V 5.5Ah, quick charger GAL 1880 CV, additional vibration control handle, safety guard, L-BOXX.

Note:

See no. 073857 ff. for suitable batteries and chargers.

Technical description

Restart block	yes
Weight	2 kg

Manufacturer's designation	GWX 18V-10 SC
Special features	Variable speed; Kickback Control; Drop Control
maximum disc Ø	125 mm
Toolholder	X-LOCK system
Battery voltage	18 V
suitable battery - supplier / battery type / voltage	Bosch 18 V
Speed range	4500 - 9000 min ⁻¹
Battery capacity	8 Ah
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
Packaging	Modular case (L-Boxx)
Power supply	Rechargeable battery-powered
Series	X-LOCK system
Type of product	Angle grinder

Accessories

Li-ion battery Battery type, battery voltage B18 V	073851 B18
Li-ion battery Battery type, battery voltage B18 V	073853 B18
Li-ion battery Battery type, battery voltage B18 V	073854 B18
Li-ion batteryProCore Battery type, battery voltage C18 V	073856 C18
Li-ion batteryProCore Battery type, battery voltage C18 V	073857 C18
Li-ion batteryProCore Battery type, battery voltage C18 V	073858 C18
Battery starter setProCore Battery type, battery voltage C18 V	073863 C18
Battery starter setProCore Battery type, battery voltage C18 V	073865 C18
Battery charger Type 1880CV	073866 1880CV
Battery charger Type GAL18160C	073866 GAL18160C

Battery starter setProCore Battery type, battery voltage C18
V

073867 C18