

Garant
Socket set 1/4 inch, Number of tools: 22

Order data

Order number	953701 22
GTIN	4062406157074
Item class	91A

Description
Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer anthracite, under which the contrast colour of blue indicates if a tool is missing.

The rigid foam inlays fill 1/4 (10 G × 8 G or 250 × 200 mm) or 1/2 (20 G × 8 G or 500 × 200 mm) of the usable drawer area.

Suitable for:

New GARANT roller cabinets with full extension drawers and a new drawer module of **20 G × 16 G** or 500 × 400 mm (W × D).

Foam inlays of size 10 G × 8 G suit shadowboards No. 923210 size 250 (2 foam inlays per shadowboard).

Supplied with:

Rigid foam inlay, empty No. 952001 size 953701: 1 pc.

GARANT hexagon socket No. 631029 size 3.5; 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13: 1 pc. each

GARANT hexagon screwdriver bit No. 631729 size 3; 4; 5; 6: 1 pc. each

GARANT reversible ratchet, No. 632025 size 1/4: 1 pc.

GARANT extension No. 632429 size 150: 1 pc.

GARANT spinner handle No. 632829 size 146: 1 pc.

GARANT T-handle No. 633029 size 116: 1 pc.

GARANT universal joint No. 633529 size 1/4: 1 pc.

Technical description

Number of tools	22
Weight	0.624 kg
Depth in G	10
Depth	250 mm
Width in G	8
Width	200 mm
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8×10
Square drive	1/4 in
Type of product	Rigid foam inlay

Accessories

Universal joint 1/4 inch Type 1/4	633529 1/4
Hexagon socket, 1/4 inch Width across flats 5 mm	631029 5
Hexagon socket, 1/4 inch Width across flats 8 mm	631029 8
Screwdriver socket, hexagon, 1/4 inch long Hexagon 3 mm	631729 3
Hexagon socket, 1/4 inch Width across flats 13 mm	631029 13
Extension, 1/4 inch overall length 150 mm	632429 150
Hexagon socket, 1/4 inch Width across flats 7 mm	631029 7
Screwdriver socket, hexagon, 1/4 inch long Hexagon 5 mm	631729 5
Spinner handle, 1/4 inch overall length 146 mm	632829 146
Hexagon socket, 1/4 inch Width across flats 6 mm	631029 6
T-handle, 1/4 inch overall length 116 mm	633029 116
Hexagon socket, 1/4 inch Width across flats 9 mm	631029 9
Hexagon socket, 1/4 inch Width across flats 10 mm	631029 10
Hexagon socket, 1/4 inch Width across flats 4 mm	631029 4

Rigid foam inlay for tool sets suitable for rigid foam set 953701	952001 953701
Screwdriver socket, hexagon, 1/4 inch long Hexagon 4 mm	631729 4
Hexagon socket, 1/4 inch Width across flats 5,5 mm	631029 5,5
Screwdriver socket, hexagon, 1/4 inch long Hexagon 6 mm	631729 6
Hexagon socket, 1/4 inch Width across flats 11 mm	631029 11
Hexagon socket, 1/4 inch Width across flats 4,5 mm	631029 4,5
Reversible ratchet, 1/4 inch with ejector Type 1/4	632025 1/4
Hexagon socket, 1/4 inch Width across flats 12 mm	631029 12
Hexagon socket, 1/4 inch Width across flats 3,5 mm	631029 3,5