



## Socket set 1/4 inch, Number of tools: 20



### Order data

|              |               |
|--------------|---------------|
| Order number | 953704 20     |
| GTIN         | 4062406157104 |
| Item class   | 91A           |

### Description

#### Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer anthracite, under which the contrast colour of blue indicates if a tool is missing.

The rigid foam inlays fill 1/4 (10 G × 8 G or 250 × 200 mm) or 1/2 (20 G × 8 G or 500 × 200 mm) of the usable drawer area.

#### Suitable for :

**New GARANT roller cabinets** with full extension drawers and a new drawer module of **20 G × 16 G** or 500 × 400 mm (W × D).

Foam inlays of size 10 G × 8 G suit shadowboards No. 923210 size 250 (2 foam inlays per shadowboard).

#### Supplied with:

Rigid foam inlay, empty No. 952001 size 953704: 1 pc.

HOLEX hexagon socket No. 631020 size 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13: 1 pc. each

HOLEX hexagon screwdriver bit No. 631720 size 3; 4; 5; 6: 1 pc. each

HOLEX reversible ratchet, No. 632090 size 1/4: 1 pc. each

HOLEX extension No. 632420 size 150: 1 pc.

HOLEX spinner handle No. 632840 size 150: 1 pc.

HOLEX T-handle No. 633029 size 116: 1 pc.

Square drive: 1/4 in

Width: 200 mm

Depth: 250 mm  
 Width in G: 8  
 Depth in G: 10  
 Weight: 0.581 kg

## Technical description

|                                     |                  |
|-------------------------------------|------------------|
| Depth                               | 250 mm           |
| Weight                              | 0.581 kg         |
| Width                               | 200 mm           |
| Depth in G                          | 10               |
| Number of tools                     | 20               |
| Width in G                          | 8                |
| Rigid foam quality LD45, thickness  | 30 mm            |
| Degree of fill of a drawer in units | 8×10             |
| Square drive                        | 1/4 in           |
| Type of product                     | Rigid foam inlay |

## Accessories

|   |            |
|---|------------|
| T-handle, 1/4 inch overall length 116 mm            | 633029 116 |
| Extension, 1/4 inch overall length 150 mm           | 632420 150 |
| Spinner handle with 1/4 inch multicraft power grip  | 632835     |
| Hexagon socket 1/4 inch Width across flats 5 mm     | 631020 5   |
| Hexagon screwdriver bit 1/4 inch short Hexagon 6 mm | 631720 6   |
| Hexagon socket 1/4 inch Width across flats 8 mm     | 631020 8   |
| Hexagon socket 1/4 inch Width across flats 12 mm    | 631020 12  |
| Hexagon socket 1/4 inch Width across flats 5,5 mm   | 631020 5,5 |
| Hexagon socket 1/4 inch Width across flats 11 mm    | 631020 11  |
| Hexagon socket 1/4 inch Width across flats 6 mm     | 631020 6   |
| Hexagon socket 1/4 inch Width across flats 4,5 mm   | 631020 4,5 |

|   |               |
|---|---------------|
| Spinner handle, 1/4 inch overall length 150                       | 632840 150    |
| Reversible ratchet, 1/4 inch with ejector                         | 632300        |
| Hexagon screwdriver bit 1/4 inch short Hexagon 5 mm               | 631720 5      |
| Hexagon socket 1/4 inch Width across flats 13 mm                  | 631020 13     |
| Hexagon socket 1/4 inch Width across flats 4 mm                   | 631020 4      |
| Hexagon socket 1/4 inch Width across flats 7 mm                   | 631020 7      |
| Hexagon socket 1/4 inch Width across flats 10 mm                  | 631020 10     |
| Hexagon socket 1/4 inch Width across flats 9 mm                   | 631020 9      |
| Reversible ratchet, 1/4 inch with ejector Type 1/4                | 632090 1/4    |
| Hexagon screwdriver bit 1/4 inch short Hexagon 3 mm               | 631720 3      |
| Rigid foam inlay for tool sets suitable for rigid foam set 953704 | 952001 953704 |
| Hexagon screwdriver bit 1/4 inch short Hexagon 4 mm               | 631720 4      |