

## Socket set 1/4 inch, Number of tools: 46



### Order data

Order number	953744 46
GTIN	2050002016897
Item class	91A

### Description

#### Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer anthracite, under which the contrast colour of blue indicates if a tool is missing.

The rigid foam inlays fill 1/4 (10 G × 8 G or 250 × 200 mm) or 1/2 (20 G × 8 G or 500 × 200 mm) of the usable drawer area.

#### Suitable for :

**New GARANT roller cabinets** with full extension drawers and a new drawer module of **20 G × 16 G** or 500 × 400 mm (W × D).

#### Supplied with:

Rigid foam inlay, empty No. 952001 size 953744: 1 pc.

GARANT hexagon socket No. 631225 size 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13; 14: 1 pc. each

HOLEX hexagon socket for Torx® No. 631515 size E4; E5; E6; E7; E8; E10: 1 pc. each

HOLEX screwdriver bit No. 631615 size 3.5; 4; 5.5; 8: 1 pc. each

HOLEX screwdriver bit for Phillips No. 631625 size 1; 2; 3; 4: 1 pc. each

GARANT hexagon screwdriver bit No. 631729 size 2.5; 3; 4; 5; 6: 1 pc. each

HOLEX screwdriver bit for Torx®, long No. 631780 size TX8; TX9; TX10; TX15; TX20; TX25; TX30; TX40: 1 pc. each

GARANT reversible ratchet, No. 632025 size 1/4: 1 pc. each

GARANT extension No. 632429 size 50; 150: 1 pc. each

GARANT spinner handle No. 632829 size 146: 1 pc.

GARANT T-handle No. 633029 size 116: 1 pc.

GARANT universal joint No. 633529 size 1/4: 1 pc.

Square drive: 1/4 in

Width: 200 mm

Depth: 500 mm

Width in G: 8  
 Depth in G: 20  
 Weight: 1.118 kg

## Technical description

Number of tools	46
Depth	500 mm
Width in G	8
Depth in G	20
Weight	1.118 kg
Width	200 mm
Version	with socket
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8×20
Square drive	1/4 in
Type of product	Rigid foam inlay

## Accessories

Hexagon socket 1/4 inch Surface Drive Width across flats 5,5 mm	631225 5,5
Hexagon socket 1/4 inch Surface Drive Width across flats 11 mm	631225 11
Hexagon socket 1/4 inch Surface Drive Width across flats 9 mm	631225 9
Torx® screwdriver bit, 1/4 inch long Torx® profile TX30	631780 TX30
Hexagon screwdriver bit 1/4 inch long Hexagon 4 mm	631729 4
Spinner handle, 1/4 inch overall length 146 mm	632829 146
Hexagon socket 1/4 inch Surface Drive Width across flats 7 mm	631225 7
Extension, 1/4 inch overall length 150 mm	632429 150

Hexagon socket 1/4 inch Surface Drive Width across flats 6 mm	631225 6
Rigid foam inlay for tool sets suitable for rigid foam set 953744	952001 953744
Socket, 1/4 inch for Torx® Torx® profile E6	631515 E6
Torx® screwdriver bit, 1/4 inch long Torx® profile TX40	631780 TX40
Hexagon screwdriver bit 1/4 inch long Hexagon 6 mm	631729 6
Torx® screwdriver bit, 1/4 inch long Torx® profile TX15	631780 TX15
Hexagon socket 1/4 inch Surface Drive Width across flats 5 mm	631225 5
Reversible ratchet, 3/8 inch with ejector Type 3/8	635025 3/8
Socket, 1/4 inch for Torx® Torx® profile E10	631515 E10
Bit for slot-head, 1/4 inch Blade width 3,5 mm	631615 3,5
Screwdriver bit for Phillips, 1/4 inch Cross-head size 1	631625 1
Hexagon socket 1/4 inch Surface Drive Width across flats 8 mm	631225 8
Hexagon screwdriver bit 1/4 inch long Hexagon 3 mm	631729 3
Extension, 1/4 inch overall length 50 mm	632429 50
Screwdriver bit for Phillips, 1/4 inch Cross-head size 2	631625 2
Socket, 1/4 inch for Torx® Torx® profile E8	631515 E8
Torx® screwdriver bit, 1/4 inch long Torx® profile TX10	631780 TX10
Bit for slot-head, 1/4 inch Blade width 5,5 mm	631615 5,5
Torx® screwdriver bit, 1/4 inch long Torx® profile TX9	631780 TX9
Torx® screwdriver bit, 1/4 inch long Torx® profile TX20	631780 TX20
Hexagon socket 1/4 inch Surface Drive Width across flats 13 mm	631225 13
Hexagon screwdriver bit 1/4 inch long Hexagon 5 mm	631729 5
Hexagon socket 1/4 inch Surface Drive Width across flats 12 mm	631225 12
T-handle, 1/4 inch overall length 116 mm	633029 116
Universal joint 1/4 inch Type 1/4	633529 1/4

Bit for slot-head, 1/4 inch Blade width 8 mm	631615 8
Hexagon socket 1/4 inch Surface Drive Width across flats 10 mm	631225 10
Torx® screwdriver bit, 1/4 inch long Torx® profile TX8	631780 TX8
Hexagon socket 1/4 inch Surface Drive Width across flats 4,5 mm	631225 4,5
Hexagon socket 1/4 inch Surface Drive Width across flats 4 mm	631225 4
Socket, 1/4 inch for Torx® Torx® profile E4	631515 E4
Socket, 1/4 inch for Torx® Torx® profile E5	631515 E5
Screwdriver bit for Phillips, 1/4 inch Cross-head size 3	631625 3
Screwdriver bit for Phillips, 1/4 inch Cross-head size 4	631625 4
Bit for slot-head, 1/4 inch Blade width 4 mm	631615 4
Hexagon screwdriver bit 1/4 inch long Hexagon 2,5 mm	631729 2,5
Torx® screwdriver bit, 1/4 inch long Torx® profile TX25	631780 TX25
Socket, 1/4 inch for Torx® Torx® profile E7	631515 E7
Hexagon socket 1/4 inch Surface Drive Width across flats 14 mm	631225 14
Reversible ratchet, 1/4 inch with ejector Type 1/4	632025 1/4