

Workshop set, Number of tools: 23



Order data

Order number	955013 23
GTIN	2050002004542
Item class	91A

Description

Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer is anthracite, the underlying contrast colour is grey, thus indicates any missing tools.

Suitable for :

GARANT roller cabinets with full extension drawers and a drawer module of **20 G × 16 G** or 500 × 400 mm (W × D).

Roller cabinets No. 914520 – 914582.

Supplied with:

Rigid foam inlay, empty No. 952001 size 955013: 1 pc.

HOLEX caliper No. 410200 size 150: 1 pc.

HOLEX locking tape measure No. 462010 size 3: 1 pc.

HOLEX aluminium spirit level No. 467435 size 300: 1 pc.

HOLEX combination spanner No. 613950 size 5.5; 7; 8; 10; 13; 16; 17; 18; 19: 1 pc. each

HOLEX slot-head screwdriver No. 660701 size 3.5; 5.5; 7: 1 pc. each

HOLEX screwdriver for Phillips No. 668401 size 1; 2; 3: 1 pc. each

HOLEX combination pliers, vanadium No. 703000 size 180: 1 pc.

HOLEX water pump pliers No. 706151 size 250: 1 pc.

HOLEX snipe-nose pliers, angled No. 713600 size 200: 1 pc.

HOLEX side cutter No. 725250 size 160: 1 pc.

GARANT universal knife No. 845020: 1 pc.

suitable for workstations and storage equipment: Roller cabinet

Width: 500 mm
 Depth: 400 mm
 Width in G: 20
 Depth in G: 16

Technical description

Depth in G	16
Number of tools	23
Width in G	20
Depth	400 mm
Width	500 mm
Version	for roller cabinet drawer
suitable for drawer front height	75 mm
suitable for drawer front height	125 mm
suitable for drawer front height	200 mm
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	20×16
suitable for workstations and storage equipment	Roller cabinet
Type of product	Rigid foam inlay

Accessories

Combination spanner Width across flats 5,5 mm	613950 5,5
Screwdriver for slot-head, with power grip Blade width b 7 mm	660701 7
Screwdriver for Phillips, with power grip Cross-head size 2	668401 2
Combination spanner Width across flats 8 mm	613950 8
Vernier caliper Vernier 1/20 Measuring range 150 mm	410200 150
Tape measure Band length 3 m	462010 3
Snipe nose pliers, angled, bright finished overall length 200 mm	713600 200

Screwdriver for Phillips, with power grip Cross-head size 1	668401 1
Rigid foam inlay for tool sets suitable for rigid foam set 955013	952001 955013
Diagonal side cutter, bright finish overall length 160 mm	725250 160
Vanadium combination pliers, bright finished overall length 180 mm	703000 180
Aluminium spirit level Length 300 mm	467435 300
Combination spanner Width across flats 18 mm	613950 18
Combination spanner Width across flats 17 mm	613950 17
Water pump pliers with plastic coating overall length 250 mm	706150 250
Screwdriver for Phillips, with power grip Cross-head size 3	668401 3
Combination spanner Width across flats 13 mm	613950 13
Combination spanner Width across flats 19 mm	613950 19
General-purpose knife with 2-component handle with 3 blades, 18 mm	845020
Screwdriver for slot-head, with power grip Blade width b 5,5 mm	660701 5,5
Combination spanner Width across flats 10 mm	613950 10
Water pump pliers with plastic coating Overall length 250 mm	706151 250
Screwdriver for slot-head, with power grip Blade width b 3,5 mm	660701 3,5
Combination spanner Width across flats 16 mm	613950 16
Combination spanner Width across flats 7 mm	613950 7