



Cordless impact wrench / impact driver, Type: GDX18200



Order data

Order number	074052 GDX18200
GTIN	3165140953863
Item class	03B

Description

Version:

Cordless impact wrench / impact driver

- **Reversible.**
- **Battery charge display.**

Universal cordless impact drill / screwdriver with **ProCORE**18V 4.0Ah battery.

- **Special tool arbor combining 1/2 inch square and 1/4 inch hexagon.**
- **3-stage PowerControl for different torques to suit different applications.**
- **Longer motor life thanks to brushless EC motor technology.**
- **Speed range settings (0 – 1100 / 2300 / 3400 rpm) and impact rate settings (0 – 2300 / 3400 / 4000 rpm).**

Advantage:

2-in-1 bit holder.

Supplied with:

Supplied with 2× Li-ion batteries, charger, L-BOXX

Note:

Suitable replacement batteries and chargers can be found under No. 073851 – 073867.

Packaging: Modular case (L-Boxx)

suitable battery - supplier / battery type / voltage: Bosch 18 V

Manufacturer's designation: GDX 18V-200 C

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion
 Battery capacity: 4 A·h
 Battery voltage: 18 V
 maximum screw Ø (8.8 - 12.9): M14

Technical description

maximum screw Ø (8.8 - 12.9)	M14
Manufacturer's designation	GDX 18V-200 C
Packaging	Modular case (L-Boxx)
Weight	1.2 kg
typical application	Strong
Number of impacts	0 - 4000 min ⁻¹
suitable battery - supplier / battery type / voltage	Bosch 18 V
maximum speed 2nd speed	2300 min ⁻¹
Tool arbor drive profile	Internal hexagon drive, external square drive
Battery voltage	18 V
maximum speed 1st speed	1100 min ⁻¹
Battery capacity	4 A·h
maximum torque hard	200 N·m
Tool arbor size	1/4 in
Tool arbor size	1/2 in
maximum vibration to EN	9.8 m/s ²
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Type of product	Impact wrench

Accessories

Li-ion battery Battery type, battery voltage B18 V	073853 B18
Battery starter set ProCore Battery type, battery voltage C18 V	073863 C18
Battery charger Type 1880CV	073866 1880CV
Li-ion battery ProCore Battery type, battery voltage C18 V	073856 C18
Battery charger Type GAL18160C	073866 GAL18160C