



## Angle grinder Cordless, Type: M18CAGXPDB



### Order data

Order number	077105 M18CAGXPDB
GTIN	4002395145805
Item class	03L

### Description

#### Version:

**Cordless angle grinder 115mm** with POWERSTATE™ motor (brushless) for very heavy-duty use. The REDLINK PLUS™ electronics offers advanced digital overload protection for machine and battery and delivers constant power even under load. With dead man's switch.

#### Supplied with:

Supplied with charger, 2× 18 V / 5.0 Ah Li-ion battery, HD box.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 18 V

Manufacturer's designation: M18CAG115XPDB-502X

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion

Battery capacity: 5 Ah

Battery voltage: 18 V

Speed range: 8500 rpm

### Technical description

maximum disc Ø	115 mm
maximum vibration to EN	2.1 m/s <sup>2</sup>
Weight	2.7 kg
Restart block	yes
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V

Battery capacity	5 Ah
Battery voltage	18 V
Speed range	8500 rpm
Manufacturer's designation	M18CAG115XPDB-502X
maximum cutting depth	28 mm
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Packaging	Modular case (HD=Heavy Duty)
Power supply	Rechargeable battery-powered
Type of product	Angle grinder

## Accessories

Li-ion battery High Output™ Battery type, battery voltage MHB3 V	073808 MHB3
Li-ion battery High Output™ Battery type, battery voltage MHB55 V	073809 MHB55
Li-ion battery High Output™ Battery type, battery voltage MHB8 V	073810 MHB8
Li-ion battery High Output™ Rechargeable battery type, battery voltage MHB12 V	073811 MHB12
Battery starter set High Output™ Type M18HNRG3	073826 M18HNRG3
Battery starter set High Output™ Type M18HNRG55	073830 M18HNRG55
Battery starter set High Output™ Type M18HNRG8	073831 M18HNRG8
Battery starter set High Output™ Type M18HNRG12	073833 M18HNRG12
Li-ion system M18B5 Rechargeable battery type, battery voltage MB18 V	073816 MB18
Li-ion system M18B2 Battery type, battery voltage MB18 V	073827 MB18
Battery starter set Type M18NRG5	073839 M18NRG5