



## Bits set "Tool-Check PLUS" with drive tool and sockets 39 pieces



### Order data

Order number	676171
GTIN	4013288191601
Item class	63H

### Description

#### Version:

Practical Kraftform Kompakt® set of bits and drive tool **for manual and machine drives**.  
**Kraftform** handle with quick-change holder for 1/4 inch bits with C 6.3 and E 6.3 shank.

#### Content:

Bits, length 25 mm, C 6.3, for Phillips: No. 675200 2 pcs. 1/25; 3 pcs. 2/25; 1 pc. 3/25  
 Bits, length 25 mm, C 6.3, for Pozidriv: No. 675380 1 pc. 1/25; 3 pcs. 2/25; 1 pc. 3/25  
 Bits, length 25 mm, C 6.3, for hex socket: 1 pc. each 675240 size 3; 4; 5; 6; 8  
 Bits, length 25 mm, C 6.3, for internal Torx®: 1 pc. each TX10; TX15; TX20; TX25; TX30; TX40  
 Bits, length 25 mm, C 6.3, for internal Torx® with pin: 1 pc. each 675350 size TX10; TX15; TX20; TX25; TX30  
 Bits, length 25 mm, C 6.3, for slot-head: 1 pc. size 1.0×5.5  
 Sockets 1/4 inch, for external hexagon: 1 pc. each size 5.5; 6; 7; 8; 10; 12; 13  
 adapter: 1 pc. 1/4 inch square socket – 1/4 inch bit holder  
 "Rapidaptor" adaptor: 1 pc. No. 675020 size 6.3K  
 Screwdriver holder: 1 pc.  
 Bit ratchet, 1/4 inch: 1 pc. No. 676645

### Technical description

Drive profile	Screwdriver for Phillips
Drive profile	Pozidriv screwdriver

Drive profile	Slot-head screwdriver
Drive profile	Hexagon screwdriver
Drive profile	Screwdriver for TORX® screws
Drive profile	Screwdriver for TORX® screws with hole
Drive profile	Hexagon socket
Manufacturer's designation	Tool-Check PLUS
Drive tool	Screwdriver holder
Drive tool	Bit ratchet, 1/4 inch
Type of product	Bit tool

## Accessories

Bit for hexagon, 1/4 inch C 6.3 Hex-plus profile Hexagon 4 mm	675240 4
Shank with magnet / quick-change coupling Hexagon shank 6,3K	675020 6,3K
Bit for Phillips, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 1/25 mm	675200 1/25
Bit for Torx®, 1/4 inch C 6.3 with bore Torx® profile TX15	675350 TX15
Bit for Torx®, 1/4 inch C 6.3 with bore Torx® profile TX20	675350 TX20
Bit for Pozidriv, 1/4 inch C 6.3, with torsion zone hard Cross-head size / overall length 3/25 mm	675380 3/25
Bit for hexagon, 1/4 inch C 6.3 Hex-plus profile Hexagon 6 mm	675240 6
Bit for hexagon, 1/4 inch C 6.3 Hex-plus profile Hexagon 8 mm	675240 8
Bit for Phillips, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 3/25 mm	675200 3/25
Bit for Torx®, 1/4 inch C 6.3 with bore Torx® profile TX10	675350 TX10
Bit for Pozidriv, 1/4 inch C 6.3, with torsion zone hard Cross-head size / overall length 2/25 mm	675380 2/25

Bit for hexagon, 1/4 inch C 6.3 Hex-plus profile Hexagon 3 mm	675240 3
Bit for hexagon, 1/4 inch C 6.3 Hex-plus profile Hexagon 5 mm	675240 5
Ratchet bit holder for 1/4 inch bits C 6.3 and E 6.3 Type 1/4	676645 1/4
Bit for Phillips, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 2/25 mm	675200 2/25
Bit for Pozidriv, 1/4 inch C 6.3, with torsion zone hard Cross-head size / overall length 1/25 mm	675380 1/25
Bit for Torx®, 1/4 inch C 6.3 with bore Torx® profile TX30	675350 TX30
Bit for Torx®, 1/4 inch C 6.3 with bore Torx® profile TX25	675350 TX25
Ratchet bit holder for 1/4 inch bits C 6.3 and E 6.3 Type	676645