

**Garant**
**Socket set 1/2 inch, Number of tools: 32**

**Order data**

Order number	953821 32
GTIN	4062406157326
Item class	91A

**Description**
**Version:**

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer anthracite**, under which the **contrast colour** of blue indicates if a tool is missing.

The rigid foam inlays fill 1/4 (10 G × 10 G or 250 × 250 mm) or 1/2 (10 G × 20 G or 250 × 500 mm) of the usable drawer area.

**Suitable for:**

New GARANT GridLine workbenches with full extension drawers and a new drawer module of 20 G × 20 G or 500 × 500 mm (W × D).

**Supplied with:**

Rigid foam inlay, empty No. 952001 size 953821: 1 pc.

GARANT reversible ratchet, No. 640025 size 1/2: 1 pc.

GARANT extension No. 641029 size 75; 125; 250: 1 pc. each

GARANT T-handle No. 641329 size 295: 1 pc.

GARANT universal joint No. 641629 size 1/2: 1 pc.

GARANT hexagon socket No. 642229 size 8; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 24; 27; 30; 32; 34: 1 pc. each

GARANT hexagon screwdriver bit No. 643229 size 4; 5; 6; 7; 8; 10; 12; 14: 1 pc. each

**Technical description**

Weight	4.236 kg
Number of tools	32

Depth in G	20
Width in G	10
Width	250 mm
Depth	500 mm
Version	with socket
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	10×20
Square drive	1/2 in
Type of product	Rigid foam inlay

## Accessories

Extension, 1/2 inch overall length 130 mm	641029 130
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 8 mm	643229 8
Hexagon socket, 1/2 inch Width across flats 19 mm	642229 19
Rigid foam inlay for tool sets suitable for rigid foam set 953821	952001 953821
Hexagon socket, 1/2 inch Width across flats 12 mm	642229 12
Hexagon socket, 1/2 inch Width across flats 22 mm	642229 22
Hexagon socket, 1/2 inch Width across flats 15 mm	642229 15
Hexagon socket, 1/2 inch Width across flats 34 mm	642229 34
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 6 mm	643229 6
Hexagon socket, 1/2 inch Width across flats 30 mm	642229 30
Hexagon socket, 1/2 inch Width across flats 27 mm	642229 27
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 14 mm	643229 14
Hexagon socket, 1/2 inch Width across flats 14 mm	642229 14
T-handle, 1/2 inch overall length 295 mm	641329 295

Universal joint, 1/2 inch Type 1/2	641629 1/2
Hexagon socket, 1/2 inch Width across flats 8 mm	642229 8
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 4 mm	643229 4
Reversible ratchet, 1/2 inch with ejector Type 1/2	640025 1/2
Hexagon socket, 1/2 inch Width across flats 16 mm	642229 16
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 12 mm	643229 12
Extension, 1/2 inch overall length 255 mm	641029 255
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 5 mm	643229 5
Hexagon socket, 1/2 inch Width across flats 18 mm	642229 18
Hexagon socket, 1/2 inch Width across flats 21 mm	642229 21
Extension, 1/2 inch overall length 75 mm	641029 75
Hexagon socket, 1/2 inch Width across flats 13 mm	642229 13
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 10 mm	643229 10
Hexagon socket, 1/2 inch Width across flats 10 mm	642229 10
Hexagon socket, 1/2 inch Width across flats 32 mm	642229 32
Hexagon socket, 1/2 inch Width across flats 24 mm	642229 24
Hexagon socket, 1/2 inch Width across flats 11 mm	642229 11
Hexagon socket, 1/2 inch Width across flats 17 mm	642229 17
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 7 mm	643229 7