

Garant
Torque wrench set 60 Nm 3/8 inch, Number of tools: 22

Order data

Order number	953961 22
GTIN	4062406157364
Item class	91A

Description
Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

Rigid foam inlay, empty No. 952001 size 953961: 1 pc.

GARANT hexagon socket No. 637125 size 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19: 1 pc. each

GARANT hexagon screwdriver bit No. 637629 size 3; 4; 5; 6; 8; 10: 1 pc. each

GARANT extension No. 635429 size 75; 125; 240: 1 pc. each

GARANT torque wrench with reversible ratchet No. 656050 size 60: 1 pc.

Technical description

Depth in G	20
Number of tools	22
Width	200 mm
Width in G	8
Number of tools	22
Depth	500 mm
Weight	1.632 kg
Rigid foam quality LD45, thickness	30 mm

Degree of fill of a drawer in units	8×20
Square drive	3/8 in
Type of product	Rigid foam inlay

Accessories

Hexagon socket, 3/8 inch Surface Drive Width across flats 11 mm	637125 11
Torque wrench with reversible ratchet maximum torque 60 N·m	656050 60
Hexagon socket, 3/8 inch Surface Drive Width across flats 19 mm	637125 19
Hexagon bit socket, 3/8 inch Hexagon 6 mm	637629 6
Extension, 3/8 inch overall length 75 mm	635429 75
Hexagon socket, 3/8 inch Surface Drive Width across flats 16 mm	637125 16
Extension, 3/8 inch overall length 240 mm	635429 240
Rigid foam inlay for tool sets suitable for rigid foam set 953961	952001 953961
Hexagon bit socket, 3/8 inch Hexagon 3 mm	637629 3
Hexagon bit socket, 3/8 inch Hexagon 5 mm	637629 5
Hexagon socket, 3/8 inch Surface Drive Width across flats 13 mm	637125 13
Hexagon socket, 3/8 inch Surface Drive Width across flats 15 mm	637125 15
Hexagon socket, 3/8 inch Surface Drive Width across flats 18 mm	637125 18
Hexagon socket, 3/8 inch Surface Drive Width across flats 14 mm	637125 14
Hexagon socket, 3/8 inch Surface Drive Width across flats 9 mm	637125 9
Hexagon bit socket, 3/8 inch Hexagon 8 mm	637629 8

Hexagon bit socket, 3/8 inch Hexagon 10 mm	637629 10
Hexagon socket, 3/8 inch Surface Drive Width across flats 17 mm	637125 17
Extension, 3/8 inch overall length 125 mm	635429 125
Hexagon socket, 3/8 inch Surface Drive Width across flats 12 mm	637125 12
Hexagon socket, 3/8 inch Surface Drive Width across flats 8 mm	637125 8
Hexagon socket, 3/8 inch Surface Drive Width across flats 10 mm	637125 10
Hexagon bit socket, 3/8 inch Hexagon 4 mm	637629 4