

Socket set 1/4 inch, Number of tools: 29



Order data

Order number	955160 29
GTIN	2050002004610
Item class	91A

Description

Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

Rigid foam inlay, empty No. 952001 size 955160: 1 pc.

GARANT hexagon socket 1/4 inch No. 631029 size 3.5; 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13; 14: 1 pc. each

HOLEX screwdriver bit 1/4 inch No. 631615 size 3.5; 5.5: 1 pc. each

HOLEX screwdriver bit for Phillips 1/4 inch No. 631625 size 1; 2: 1 pc. each

GARANT hexagon screwdriver bit 1/4 inch long No. 631729 size 2.5; 3; 4; 5; 6: 1 pc. each

GARANT reversible ratchet, 1/4 inch No. 632025 size 1/4: 1 pc.

GARANT extension 1/4 inch No. 632429 size 50; 100: 1 pc. each

GARANT spinner handle 1/4 inch No. 632829 size 146: 1 pc.

GARANT T-handle 1/4 inch No. 633029 size 116: 1 pc.

GARANT universal joint 1/4 inch No. 633529 size 1/4: 1 pc.

suitable for shadowboard depth: 115 mm

Width: 383 mm

Depth: 115 mm

Technical description

Number of tools	29
Width	383 mm
Depth	115 mm

Version	with socket
Rigid foam quality LD45, thickness	30 mm
Square drive	1/4 in
suitable for shadowboard depth	115 mm
Type of product	Rigid foam inlay

Accessories

Spinner handle, 1/4 inch overall length 146 mm	632829 146
Reversible ratchet, 1/4 inch with ejector Type 1/4	632025 1/4
Bit for slot-head, 1/4 inch Blade width 3,5 mm	631615 3,5
Hexagon socket 1/4 inch Width across flats 4 mm	631029 4
Extension, 1/4 inch overall length 100 mm	632429 100
Hexagon screwdriver bit 1/4 inch long Hexagon 3 mm	631729 3
Hexagon socket 1/4 inch Width across flats 8 mm	631029 8
Screwdriver bit for Phillips, 1/4 inch Cross-head size 1	631625 1
Universal joint 1/4 inch Type 1/4	633529 1/4
Screwdriver bit for Phillips, 1/4 inch Cross-head size 2	631625 2
Hexagon socket 1/4 inch Width across flats 5 mm	631029 5
Hexagon screwdriver bit 1/4 inch long Hexagon 2,5 mm	631729 2,5
Extension, 1/4 inch overall length 50 mm	632429 50
Hexagon socket 1/4 inch Width across flats 14 mm	631029 14
Hexagon socket 1/4 inch Width across flats 6 mm	631029 6
Hexagon socket 1/4 inch Width across flats 13 mm	631029 13
T-handle, 1/4 inch overall length 116 mm	633029 116
Hexagon socket 1/4 inch Width across flats 4,5 mm	631029 4,5
Hexagon socket 1/4 inch Width across flats 3,5 mm	631029 3,5
Hexagon socket 1/4 inch Width across flats 10 mm	631029 10
Hexagon socket 1/4 inch Width across flats 5,5 mm	631029 5,5

Hexagon socket 1/4 inch Width across flats 12 mm	631029 12
Hexagon socket 1/4 inch Width across flats 11 mm	631029 11
Hexagon screwdriver bit 1/4 inch long Hexagon 4 mm	631729 4
Hexagon screwdriver bit 1/4 inch long Hexagon 6 mm	631729 6
Bit for slot-head, 1/4 inch Blade width 5,5 mm	631615 5,5
Hexagon screwdriver bit 1/4 inch long Hexagon 5 mm	631729 5
Hexagon socket 1/4 inch Width across flats 9 mm	631029 9
Hexagon socket 1/4 inch Width across flats 7 mm	631029 7
Rigid foam inlay for tool sets suitable for rigid foam set 955160	952001 955160
Reversible ratchet, 1/4 inch with ejector Type	632025